

Varistar CP Side Panel With Quick-Release Fastener and Lock

带速卸锁扣的 Varistar 侧面板，不带接地套件。



功能

碳钢, 1 mm

侧面板，不带接地

包括安全锁套件

技术参数

产品类型: 机柜/机架面板

防护等级: IP20

Table 1/2

物料号	机架高度	高度	深度	包装数量	颜色	颜色代码
21630-285	24U	1200mm	600mm	2	暗灰色	RAL 7021
21630-286	24U	1200mm	800mm	2	暗灰色	RAL 7021
21630-289	29U	1400mm	600mm	2	暗灰色	RAL 7021
21630-290	29U	1400mm	800mm	2	暗灰色	RAL 7021

物料号	机架高度	高度	深度	包装数量	颜色	颜色代码
21630-293	33U	1600mm	600mm	2	暗灰色	RAL 7021
21630-294	33U	1600mm	800mm	2	暗灰色	RAL 7021
21630-297	38U	1800mm	600mm	2	暗灰色	RAL 7021
21630-298	38U	1800mm	800mm	2	暗灰色	RAL 7021
21630-302	42U	2000mm	600mm	2	暗灰色	RAL 7021
21630-303	42U	2000mm	800mm	2	暗灰色	RAL 7021
21630-304	42U	2000mm	900mm	2	暗灰色	RAL 7021
21630-064	42U	2000mm	1000mm	2	暗灰色	RAL 7021
21630-306	47U	2200mm	600mm	2	暗灰色	RAL 7021
21630-307	47U	2200mm	800mm	2	暗灰色	RAL 7021
21630-308	47U	2200mm	900mm	2	暗灰色	RAL 7021
21630-070	47U	2200mm	1000mm	2	暗灰色	RAL 7021
21630-287	24U	1200mm	900mm	2	暗灰色	RAL 7021
21630-288	24U	1200mm	1000mm	2	暗灰色	RAL 7021
21630-291	29U	1400mm	900mm	2	暗灰色	RAL 7021
21630-292	29U	1400mm	1000mm	2	暗灰色	RAL 7021
21630-295	33U	1600mm	900mm	2	暗灰色	RAL 7021

物料号	机架高度	高度	深度	包装数量	颜色	颜色代码
21630-296	33U	1600mm	1000mm	2	暗灰色	RAL 7021
21630-299	38U	1800mm	900mm	2	暗灰色	RAL 7021
21630-300	38U	1800mm	1000mm	2	暗灰色	RAL 7021
21630-065	42U	2000mm	1100mm	2	暗灰色	RAL 7021
21630-066	42U	2000mm	1200mm	2	暗灰色	RAL 7021
21630-071	47U	2200mm	1100mm	2	暗灰色	RAL 7021
21630-072	47U	2200mm	1200mm	2	暗灰色	RAL 7021

Table 2/2				
物料号	完成	材料	类型	快速发货
21630-285	粉末涂层	钢	侧板, 快拆	No
21630-286	粉末涂层	钢	侧板, 快拆	No
21630-289	粉末涂层	钢	侧板, 快拆	No
21630-290	粉末涂层	钢	侧板, 快拆	No
21630-293	粉末涂层	钢	侧板, 快拆	No
21630-294	粉末涂层	钢	侧板, 快拆	No
21630-297	粉末涂层	钢	侧板, 快拆	No
21630-298	粉末涂层	钢	侧板, 快拆	No

物料号	完成	材料	类型	快速发货
21630-302	粉末涂层	钢	侧板, 快拆	No
21630-303	粉末涂层	钢	侧板, 快拆	No
21630-304	粉末涂层	钢	侧板, 快拆	No
21630-064	粉末涂层	钢	侧板, 快拆	No
21630-306	粉末涂层	钢	侧板, 快拆	No
21630-307	粉末涂层	钢	侧板, 快拆	No
21630-308	粉末涂层	钢	侧板, 快拆	No
21630-070	粉末涂层	钢	侧板, 快拆	No
21630-287	粉末涂层	钢	侧板, 快拆	No
21630-288	粉末涂层	钢	侧板, 快拆	No
21630-291	粉末涂层	钢	侧板, 快拆	No
21630-292	粉末涂层	钢	侧板, 快拆	No
21630-295	粉末涂层	钢	侧板, 快拆	No
21630-296	粉末涂层	钢	侧板, 快拆	No
21630-299	粉末涂层	钢	侧板, 快拆	No
21630-300	粉末涂层	钢	侧板, 快拆	No
21630-065	粉末涂层	钢	侧板, 快拆	No

物料号	完成	材料	类型	快速发货
21630-066	粉末涂层	钢	侧板，快拆	No
21630-071	粉末涂层	钢	侧板，快拆	No
21630-072	粉末涂层	钢	侧板，快拆	No

其他产品详情

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE