

Varistar CP 钢板门, Plain With 3-Point Locking, IP55



内部装有安装框架的钢制门，3点锁定，带拥有内置按钮的摇柄锁。

功能

带 IP 55 防护等级三点锁的钢门

带按钮的摇柄把手

开门角度 180°

技术参数

锁定类型: 3 点锁定

产品类型: 机柜门

防护等级: IP55

材料: 钢

Table 1/2

物料号	机架高度	高度	宽度	包装数量	颜色	颜色代码
21630-210	24U	1200mm	600mm	1	暗灰色	RAL 7021
21630-216	24U	1200mm	800mm	1	暗灰色	RAL 7021
21630-211	29U	1400mm	600mm	1	暗灰色	RAL 7021

物料号	机架高度	高度	宽度	包装数量	颜色	颜色代码
21630-217	29U	1400mm	800mm	1	暗灰色	RAL 7021
21630-212	33U	1600mm	600mm	1	暗灰色	RAL 7021
21630-218	33U	1600mm	800mm	1	暗灰色	RAL 7021
21630-213	38U	1800mm	600mm	1	暗灰色	RAL 7021
21630-219	38U	1800mm	800mm	1	暗灰色	RAL 7021
21630-214	42U	2000mm	600mm	1	暗灰色	RAL 7021
21630-220	42U	2000mm	800mm	1	暗灰色	RAL 7021
21630-215	47U	2200mm	600mm	1	暗灰色	RAL 7021
21630-171	47U	2200mm	800mm	1	暗灰色	RAL 7021

Table 2/2					
物料号	符合	完成	类型	搭配	快速发货
21630-210	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-216	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-211	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-217	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-212	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-218	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No

物料号	符合	完成	类型	搭配	快速发货
21630-213	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-219	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-214	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-220	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-215	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No
21630-171	IEC 61587-1	粉末涂层	钢板门	Varistar CP	No

其他产品详情

请单独订购适用于摇柄把手的 DIN 锁芯。

请单独购买接地套件。

警告

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE