

Шкаф Varistar для совместного размещения оборудования, RAL 7035

Data Solutions



Шкафы для совместного размещения оборудования с 2, 3 или 4 отсеками в цвете RAL 7035 для установки серверов с возможностью разделения доступа и организации кабелей.

CERTIFICATIONS



FEATURES

Шкафы для совместного размещения оборудования с отсеками для размещения, например, серверов

Гибкая разводка кабелей, возможна сверху, снизу, слева или справа (кабели передачи данных и питания можно прокладывать отдельно)

Многоточечное запирание дверей

Перфорированные двери

Степень защиты IP 20

Цвет RAL 7035

SPECIFICATIONS

Product Type:	Rack
Frame Material:	Сталь

Table 1/3

Catalog Number	Rack Height	Высота мм	Cladding Material	Frame Color	Ширина мм	Frame Color Code
11130-202	40U	2000mm	Сталь	Light Grey	600mm	RAL 7021
11130-203	39U	2000mm	Сталь	Light Grey	600mm	RAL 7021
11130-204	40U	2000mm	Сталь	Light Grey	600mm	RAL 7021
11130-205	40U	2000mm	Сталь	Light Grey	800mm	RAL 7021
11130-206	39U	2000mm	Сталь	Light Grey	800mm	RAL 7035
11130-207	40U	2000mm	Сталь	Light Grey	800mm	RAL 7021
11130-208	44U	2200mm	Сталь	Light Grey	600mm	RAL 7021
11130-209	45U	2200mm	Сталь	Light Grey	600mm	RAL 7021
11130-210	44U	2200mm	Сталь	Light Grey	600mm	RAL 7021
11130-211	44U	2200mm	Сталь	Light Grey	800mm	RAL 7021
11130-212	45U	2200mm	Сталь	Black Grey	800mm	RAL 7021
11130-213	44U	2200mm	Сталь	Light Grey	800mm	RAL 7021
11130-214	40U	2000mm	Сталь	Light Grey	600mm	RAL 7021
11130-215	39U	2000mm	Сталь	Light Grey	600mm	RAL 7021
11130-216	40U	2000mm	Сталь	Light Grey	600mm	RAL 7021
11130-217	40U	2000mm	Сталь	Light Grey	800mm	RAL 7021
11130-218	39U	2000mm	Сталь	Black Grey	800mm	RAL 7021
11130-219	40U	2000mm	Сталь	Light Grey	800mm	RAL 7021

CatalogNumber	Rack Height	Высота мм	Cladding Material	Frame Color	Ширина мм	Frame Color Code
11130-220	44U	2200mm	Сталь	Light Grey	600mm	RAL 7021
11130-221	45U	2200mm	Сталь	Light Grey	600mm	RAL 7021
11130-222	44U	2200mm	Сталь	Light Grey	600mm	RAL 7021
11130-223	44U	2200mm	Сталь	Light Grey	800mm	RAL 7021
11130-224	45U	2200mm	Сталь	Light Grey	800mm	RAL 7021
11130-225	44U	2200mm	Сталь	Light Grey	800mm	RAL 7021
11130-257	45U	2450mm	Сталь	Light Grey	600mm	RAL 7021
11130-258	48U	2450mm	Сталь	Light Grey	600mm	RAL 7021
11130-259	48U	2450mm	Сталь	Light Grey	600mm	RAL 7021
11130-260	45U	2450mm	Сталь	Light Grey	800mm	RAL 7021
11130-261	48U	2450mm	Сталь	Light Grey	800mm	RAL 7021
11130-262	48U	2450mm	Сталь	Light Grey	800mm	RAL 7021
11130-269	45U	2450mm	Сталь	Light Grey	600mm	RAL 7021
11130-270	48U	2450mm	Сталь	Light Grey	600mm	RAL 7021
11130-271	48U	2450mm	Сталь	Light Grey	600mm	RAL 7021
11130-272	45U	2450mm	Сталь	Light Grey	800mm	RAL 7021
11130-273	48U	2450mm	Сталь	Light Grey	800mm	RAL 7021
11130-274	48U	2450mm	Сталь	Light Grey	800mm	RAL 7021

Table 2/3

Catalog Number	Cladding Color	Cladding Color Code	Глубина мм	Package Quantity	Number of Compartments	Finish
11130-202	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-203	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-204	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-205	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-206	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-207	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-208	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-209	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-210	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-211	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-212	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-213	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-214	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-215	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-216	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-217	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-218	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-219	Light Grey	RAL 7035	1200mm	1	4	Powder Coated

CatalogNumber	Cladding Color	Cladding Color Code	Глубина мм	Package Quantity	Number of Compartments	Finish
11130-220	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-221	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-222	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-223	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-224	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-225	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-257	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-258	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-259	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-260	Light Grey	RAL 7035	1000mm	1	2	Powder Coated
11130-261	Light Grey	RAL 7035	1000mm	1	3	Powder Coated
11130-262	Light Grey	RAL 7035	1000mm	1	4	Powder Coated
11130-269	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-270	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-271	Light Grey	RAL 7035	1200mm	1	4	Powder Coated
11130-272	Light Grey	RAL 7035	1200mm	1	2	Powder Coated
11130-273	Light Grey	RAL 7035	1200mm	1	3	Powder Coated
11130-274	Light Grey	RAL 7035	1200mm	1	4	Powder Coated

Table 3/3

Catalog Number	Material	Static Load
11130-202	Сталь	800kg
11130-203	Сталь	800kg
11130-204	Сталь	800kg
11130-205	Сталь	800kg
11130-206	Сталь	800kg
11130-207	Сталь	800kg
11130-208	Сталь	800kg
11130-209	Сталь	800kg
11130-210	Сталь	800kg
11130-211	Сталь	800kg
11130-212	Сталь	800kg
11130-213	Сталь	800kg
11130-214	Сталь	800kg
11130-215	Сталь	800kg
11130-216	Сталь	800kg
11130-217	Сталь	800kg
11130-218	Сталь	800kg
11130-219	Сталь	800kg

Catalog Number	Material	Static Load
11130-220	Сталь	800kg
11130-221	Сталь	800kg
11130-222	Сталь	800kg
11130-223	Сталь	800kg
11130-224	Сталь	800kg
11130-225	Сталь	800kg
11130-257	Сталь	800kg
11130-258	Сталь	800kg
11130-259	Сталь	800kg
11130-260	Сталь	800kg
11130-261	Сталь	800kg
11130-262	Сталь	800kg
11130-269	Сталь	800kg
11130-270	Сталь	800kg
11130-271	Сталь	800kg
11130-272	Сталь	800kg
11130-273	Сталь	800kg
11130-274	Сталь	800kg

ADDITIONAL PRODUCT DETAILS

Боковая панель заказывается отдельно. Информацию о подходящей кабельной панели см. в разделе «Принадлежности».

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte