

Шкаф Varistar для совместного размещения оборудования, RAL 9003

Data Solutions



Шкафы для совместного размещения оборудования с 2, 3 или 4 отсеками в цвете RAL 9003 для установки серверов с возможностью разделения доступа и организации кабелей.

CERTIFICATIONS



FEATURES

Шкафы для совместного размещения оборудования с отсеками для размещения, например, серверов

Гибкая разводка кабелей, возможна сверху, снизу, слева или справа (кабели передачи данных и питания можно прокладывать отдельно)

Многоточечное запирание дверей

Перфорированные двери

Степень защиты IP 20

Цвет RAL 9003

SPECIFICATIONS

Product Type:	Rack
Frame Material:	Сталь

Table 1/3

Catalog Number	Rack Height	Высота мм	Cladding Material	Frame Color	Ширина мм	Frame Color Code
12130-202	40U	2000mm	Сталь	Signal White	600mm	RAL 7021
12130-203	39U	2000mm	Сталь	Signal White	600mm	RAL 7021
12130-204	40U	2000mm	Сталь	Signal White	600mm	RAL 7021
12130-205	40U	2000mm	Сталь	Signal White	800mm	RAL 7021
12130-206	39U	2000mm	Сталь	Black Grey	800mm	RAL 7021
12130-207	40U	2000mm	Сталь	Signal White	800mm	RAL 7021
12130-208	44U	2200mm	Сталь	Signal White	600mm	RAL 7021
12130-209	45U	2200mm	Сталь	Signal White	600mm	RAL 7021
12130-210	44U	2200mm	Сталь	Signal White	600mm	RAL 7021
12130-211	44U	2200mm	Сталь	Signal White	800mm	RAL 7021
12130-212	45U	2200mm	Сталь	Black Grey	800mm	RAL 7021
12130-213	44U	2200mm	Сталь	Signal White	800mm	RAL 7021
12130-214	40U	2000mm	Сталь	Signal White	600mm	RAL 7021
12130-215	39U	2000mm	Сталь	Signal White	600mm	RAL 7021
12130-216	40U	2000mm	Сталь	Signal White	600mm	RAL 7021
12130-217	40U	2000mm	Сталь	Signal White	800mm	RAL 7021
12130-218	39U	2000mm	Сталь	Black Grey	800mm	RAL 7021
12130-219	40U	2000mm	Сталь	Signal White	800mm	RAL 7021

CatalogNumber	Rack Height	Высота мм	Cladding Material	Frame Color	Ширина мм	Frame Color Code
12130-220	44U	2200mm	Сталь	Signal White	600mm	RAL 7021
12130-221	45U	2200mm	Сталь	Signal White	600mm	RAL 7021
12130-222	44U	2200mm	Сталь	Signal White	600mm	RAL 7021
12130-223	44U	2200mm	Сталь	Signal White	800mm	RAL 7021
12130-224	45U	2200mm	Сталь	Signal White	800mm	RAL 7021
12130-225	44U	2200mm	Сталь	Signal White	800mm	RAL 7021
12130-257	45U	2450mm	Сталь	Signal White	600mm	RAL 7021
12130-258	48U	2450mm	Сталь	Signal White	600mm	RAL 7021
12130-259	48U	2450mm	Сталь	Signal White	600mm	RAL 7021
12130-260	45U	2450mm	Сталь	Signal White	800mm	RAL 7021
12130-261	48U	2450mm	Сталь	Signal White	800mm	RAL 7021
12130-262	48U	2450mm	Сталь	Signal White	800mm	RAL 7021
12130-269	45U	2450mm	Сталь	Signal White	600mm	RAL 7021
12130-270	48U	2450mm	Сталь	Signal White	600mm	RAL 7021
12130-271	48U	2450mm	Сталь	Signal White	600mm	RAL 7021
12130-272	45U	2450mm	Сталь	Signal White	800mm	RAL 7021
12130-273	48U	2450mm	Сталь	Signal White	800mm	RAL 7021
12130-274	48U	2450mm	Сталь	Signal White	800mm	RAL 7021

Table 2/3

Catalog Number	Cladding Color	Cladding Color Code	Глубина мм	Package Quantity	Number of Compartments	Finish
12130-202	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-203	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-204	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-205	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-206	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-207	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-208	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-209	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-210	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-211	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-212	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-213	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-214	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-215	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-216	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-217	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-218	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-219	Signal White	RAL 9003	1200mm	1	4	Powder Coated

CatalogNumber	Cladding Color	Cladding Color Code	Глубина мм	Package Quantity	Number of Compartments	Finish
12130-220	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-221	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-222	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-223	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-224	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-225	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-257	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-258	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-259	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-260	Signal White	RAL 9003	1000mm	1	2	Powder Coated
12130-261	Signal White	RAL 9003	1000mm	1	3	Powder Coated
12130-262	Signal White	RAL 9003	1000mm	1	4	Powder Coated
12130-269	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-270	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-271	Signal White	RAL 9003	1200mm	1	4	Powder Coated
12130-272	Signal White	RAL 9003	1200mm	1	2	Powder Coated
12130-273	Signal White	RAL 9003	1200mm	1	3	Powder Coated
12130-274	Signal White	RAL 9003	1200mm	1	4	Powder Coated

Table 3/3

Catalog Number	Material	Static Load
12130-202	Сталь	800kg
12130-203	Сталь	800kg
12130-204	Сталь	800kg
12130-205	Сталь	800kg
12130-206	Сталь	800kg
12130-207	Сталь	800kg
12130-208	Сталь	800kg
12130-209	Сталь	800kg
12130-210	Сталь	800kg
12130-211	Сталь	800kg
12130-212	Сталь	800kg
12130-213	Сталь	800kg
12130-214	Сталь	800kg
12130-215	Сталь	800kg
12130-216	Сталь	800kg
12130-217	Сталь	800kg
12130-218	Сталь	800kg
12130-219	Сталь	800kg

Catalog Number	Material	Static Load
12130-220	Сталь	800kg
12130-221	Сталь	800kg
12130-222	Сталь	800kg
12130-223	Сталь	800kg
12130-224	Сталь	800kg
12130-225	Сталь	800kg
12130-257	Сталь	800kg
12130-258	Сталь	800kg
12130-259	Сталь	800kg
12130-260	Сталь	800kg
12130-261	Сталь	800kg
12130-262	Сталь	800kg
12130-269	Сталь	800kg
12130-270	Сталь	800kg
12130-271	Сталь	800kg
12130-272	Сталь	800kg
12130-273	Сталь	800kg
12130-274	Сталь	800kg

ADDITIONAL PRODUCT DETAILS

Боковая панель заказывается отдельно. Информацию о подходящей кабельной панели см. в разделе «Принадлежности».

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE