

绝缘安装面板，AMI



该安装板易于加工，可以防止电气组件和机柜之间发生意外接触。

功能

Description: Insulated mounting plate for wall mounted enclosures. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Bakelite.

Pack quantity: 1 piece.

技术参数

厚度: 4mm
材料: 胶木
颜色: 黑色
完成: 平滑

Table 1/1						
物料号	订货号	高度	宽度	深度	面板尺寸	外壳材料
AMI02020	AMI02020	200mm	200mm	4mm	170 x 150mm	低碳钢
AMI02520	AMI02520	250mm	200mm	4mm	220 x 150mm	低碳钢
AMI02525	AMI02525	250mm	250mm	4mm	220 x 200mm	低碳钢
AMI03025	AMI03025	300mm	250mm	4mm	270 x 200mm	低碳钢
AMI03030	AMI03030	300mm	300mm	4mm	270 x 250mm	低碳钢
AMI03040		300mm	400mm	4mm	270 x 350mm	低碳钢
AMI03525		350mm	250mm	4mm	320 x 200mm	低碳钢
AMI04030	AMI04030	400mm	300mm	4mm	370 x 250mm	低碳钢
AMI04040	AMI04040	400mm	400mm	4mm	370 x 350mm	低碳钢
AMI04050		400mm	500mm	4mm	370 x 450mm	低碳钢
AMI04060	AMI04060	400mm	600mm	4mm	370 x 550mm	低碳钢
AMI05030	AMI05030	500mm	300mm	4mm	470 x 250mm	低碳钢
AMI05040	AMI05040	500mm	400mm	4mm	470 x 350mm	低碳钢
AMI05050	AMI05050	500mm	500mm	4mm	470 x 450mm	低碳钢
AMI06040	AMI06040	600mm	400mm	4mm	570 x 350mm	低碳钢

物料号	订货号	高度	宽度	深度	面板尺寸	外壳材料
AMI06050	AMI06050	600mm	500mm	4mm	570 x 450mm	低碳钢
AMI06060	AMI06060	600mm	600mm	4mm	570 x 550mm	低碳钢
AMI06080	AMI06080	600mm	800mm	4mm	570 x 750mm	低碳钢
AMI07050	AMI07050	700mm	500mm	4mm	670 x 450mm	低碳钢
AMI08040		800mm	400mm	4mm	770 x 350mm	低碳钢
AMI08060	AMI08060	800mm	600mm	4mm	770 x 550mm	低碳钢
AMI08080		800mm	800mm	4mm	770 x 750mm	低碳钢
AMI10060	AMI10060	1000mm	600mm	4mm	970 x 550mm	低碳钢
AMI10080	AMI10080	1000mm	800mm	4mm	970 x 750mm	低碳钢
AMI12060		1200mm	600mm	4mm	1170 x 550mm	低碳钢
AMI12080	AMI12080	1200mm	800mm	4mm	1170 x 750mm	低碳钢

其他产品详情

Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE