

# Slotted Front Panels For Power Distribution, MSMCP



This mild steel slotted front panel, MSMCP, is for the front frame of a fix system, or modular frames. No machining is required when it is used for mounting modular components.

## 功能

Description: Slotted front panel for modular assemblies. Provided with one DIN rail per row for modular components. It has a top and bottom bending to provide extra rigidity.

Material: 1.25 mm steel.

Finish: RAL 7035 structured powder coating.

Delivery: 1 piece with mounting material.

Mounting requirements: To be assembled on the modular system frame.

The panels are to be mounted onto a fix system front frame (MSFCP) or onto modular system frames (MSMSF or MSMSM)

Slotted front panel for modular assemblies

Provided with one DIN rail per row for modular components

It has a top and bottom bending to provide extra rigidity

One piece with mounting material

To be assembled on the modular system frame

技术参数

厚度: 1.25mm  
颜色: 浅灰色  
材料: 低碳钢  
完成: 粉末涂层  
颜色代码: RAL 7035

| Table 1/1     |       |       |      |      |           |      |
|---------------|-------|-------|------|------|-----------|------|
| 物料号           | 高度    | 宽度    | 深度   | 外壳材料 | 产品系列      | 面板数量 |
| MSMCP1506R5   | 150mm | 600mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 1    |
| MSMCP1508R5   | 150mm | 800mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 1    |
| MSMCP2006R5   | 200mm | 600mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 1    |
| MSMCP2008R5   | 200mm | 800mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 1    |
| MSMCP3006-1R5 | 300mm | 600mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 1    |
| MSMCP3006-2R5 | 300mm | 600mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 2    |
| MSMCP3008-1R5 | 300mm | 800mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 1    |
| MSMCP3008-2R5 | 300mm | 800mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 2    |
| MSMCP4506R5   | 450mm | 600mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 3    |
| MSMCP4508R5   | 450mm | 800mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 3    |
| MSMCP6006R5   | 600mm | 600mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 4    |
| MSMCP6008R5   | 600mm | 800mm | 13mm | 低碳钢  | 独立, 壁挂式安装 | 4    |

## 警告

---

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**