

Socket Strip, SCHUKO

Power Utilities



Modular, compact PDU with many function elements. Using a 1U by 1U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

认证



功能

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

技术参数

Table 1/2

物料号	插座类型	交流电压	功能	颜色	深度	长度
-----	------	------	----	----	----	----

60110-266	SCHUKO	230 V	瞬态保护, 电源抑制过滤器	灰色	44 mm	438.5 mm
60110-207	SCHUKO	230 V		灰色	44 mm	947.5 mm
60110-208	SCHUKO	230 V		灰色	44 mm	1202 mm
60110-206	SCHUKO	230 V		灰色	44 mm	438.5 mm
60110-205	SCHUKO	230 V		灰色	44 mm	1753 mm
60110-209	SCHUKO	230 V		灰色	44 mm	1753 mm
60110-204	SCHUKO	230 V		灰色	44 mm	1202 mm
60110-210	SCHUKO	230 V	瞬态保护	灰色	44 mm	438.5 mm
60110-203	SCHUKO	230 V		灰色	44 mm	947.5 mm
60110-214	SCHUKO	230 V	电源抑制过滤器	灰色	44 mm	438.5 mm
60110-202	SCHUKO	230 V		灰色	44 mm	438.5 mm
60110-211	SCHUKO	230 V	瞬态保护	灰色	44 mm	947.5 mm
60110-201	SCHUKO	230 V		灰色	44 mm	210 mm
60110-200	SCHUKO	230 V		灰色	44 mm	184 mm
60110-212	SCHUKO	230 V	过流保护	灰色	75 mm	438.5 mm
60110-216	SCHUKO	230 V	故障电流保护	灰色	88 mm	438.5 mm
60110-217	SCHUKO	230 V	故障电流保护, 过流保护	灰色	88 mm	438.5 mm

Table 2/2

物料号	产品类型
60110-266	插排
60110-207	插排
60110-208	插排
60110-206	插排
60110-205	插排
60110-209	插排
60110-204	插排
60110-210	插排
60110-203	插排
60110-214	插排
60110-202	插排
60110-211	插排
60110-201	插排
60110-200	插排
60110-212	插排
60110-216	插排

物料号	产品类型
60110-217	插排

其他产品详情

Please order mounting bracket for vertical mounting separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE