


Дефлектор, U-образная передняя панель, возможно дооснащение экранированием, текстиль



Дефлектор с U-образной передней панелью закрывает пустой слот, чтобы исключить выход воздушного потока. U-образная передняя панель допускает использование текстильной прокладки ЭМС.

CERTIFICATIONS



FEATURES

Дефлектор исключает утечку воздуха из пустых слотов

Крышка вставляется в направляющую

SPECIFICATIONS

Product Type:	Air Baffle
Material:	Алюминий
Finish:	Anodized; Passivated
Product Family:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
Type:	With Front Panel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Глубина мм	EMC Shielding	Rack Width	Works With
----------------	-------------	------------------	------------	---------------	------------	------------

20848-728	3U	1	160mm	No (Retrofittable)	4HP	Блочный каркас, Coffrets
20848-737	6U	1	220mm	No (Retrofittable)	4HP	Блочный каркас, Coffrets
20848-736	6U	1	160mm	No (Retrofittable)	4HP	Блочный каркас, Coffrets
20848-729	3U	1	220mm	No (Retrofittable)	4HP	Блочный каркас, Coffrets

Table 2/2

Catalog Number	Quick Ship
20848-728	No
20848-737	No
20848-736	No
20848-729	No

ADDITIONAL PRODUCT DETAILS

Дефлекторы для плат глубиной 280 мм и для задних плат ввода/вывода глубиной 80 мм доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE