

19" 抽屉，带键盘 1 U, 触摸板, RAL 9005

19" 机架安装键盘抽屉，带全延长键盘。



认证



功能

带键盘的可扩展 1 U 抽屉，包括功能键、数字垫、触摸板

可在完全延长和收缩状态下保持位置锁定

连接到用于键盘和鼠标的 USB

安装尺寸，19" 轨道距离（c 尺寸）：470 ... 700 mm

亮黑色 (RAL 9005)

技术参数

产品类型： 机柜/机架抽屉

Table 1/2

物料号	机架高度	深度	颜色	包装数量	颜色代码	类型
60118-566	1U	400mm	墨黑色	1	RAL 9005	键盘

物料号	机架高度	深度	颜色	包装数量	颜色代码	类型
60118-569	1U	400mm	墨黑色	1	RAL 9005	键盘
60118-568	1U	400mm	墨黑色	1	RAL 9005	键盘
60118-567	1U	400mm	墨黑色	1	RAL 9005	键盘

Table 2/2			
物料号	搭配	键盘类型	快速发货
60118-566	19" 机柜	QWERTZ	No
60118-569	19" 机柜	QWERTY 英式	No
60118-568	19" 机柜	AZERTY	No
60118-567	19" 机柜	QWERTY 美式	No

其他产品详情

应要求提供其他键盘布局、轨迹球和连接。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE