


Горизонтальная рейка, передняя, тип R-LD, прочная, с длинной кромкой, 63 HP

CATALOG NUMBER

34566-363



Combinations of horizontal rails and side panels

	Side panel	Light < 1	Frontier 1	Heavy < 10	Rugged < 10
Standard rail	+	+	+	+	+
Standard rail with front panel	+	+	+	+	+
Standard rail with side panel	+	+	+	+	+
Standard rail with front and side panels	+	+	+	+	+

Legend: "+" can be combined, "-" combination not recommended

Прочная горизонтальная рейка выдерживает удары и вибрацию до 25 g. Это позволяет использовать ручки - экстракторы IEEE.

CERTIFICATIONS



FEATURES

Прочные горизонтальные рейки типа R-LD с креплением на 3 отверстия для повышенной прочности

Для установки и извлечения плат CompactPCI, VME64x

С HP-маркировкой от 28 HP

Длина 20, 28, 40, 42, 63, 84 HP или 1000 мм

Алюминиевый экструдированный профиль, анодированная поверхность, электропроводящая контактная поверхность, с маркировкой HP

PRODUCT ATTRIBUTES

Rack Width: 63HP

Package Quantity: 1

Finish: Anodized

Длина мм: 325.12mm

Material: Алюминий

Product Family: EuropacPRO

Product Type: Горизонтальный рельс

Type: Rugged, LD

Works With: Блочный каркас

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE