


# EuropacPRO Advanced EMC 45 Top and Bottom Covers, Screwed to Side Panel, Ø 2.3mm



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

## 认证



## 功能

Top and bottom covers with EMC and airflow optimized perforation, fulfills the requirements of the fire safety standard EN 62368-1, perforation diameter Ø 2.3mm, degree 50%

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Cover plate for bolting to the side panel

Suitable for use with all horizontal rails, besides Rugged

## 技术参数

|       |            |
|-------|------------|
| 材料:   | 铝          |
| 产品类型: | 盖板         |
| 产品系列: | EuropacPRO |
| 完成:   | 钝化         |

类型: 穿孔  
搭配: 插箱

Table 1/1

| 物料号       | 机架宽度 | 深度       | 包装数量 | 包装单位 | 快速发货 |
|-----------|------|----------|------|------|------|
| 24563-555 | 36HP | 175mm    | 2    | 对    | No   |
| 24563-556 | 36HP | 235mm    | 2    | 对    | No   |
| 24563-560 | 42HP | 175mm    | 2    | 对    | No   |
| 24563-561 | 42HP | 235mm    | 2    | 对    | No   |
| 24563-562 | 42HP | 275mm    | 2    | 对    | No   |
| 24563-563 | 42HP | 277.75mm | 2    | 对    | No   |
| 24563-564 | 42HP | 295mm    | 2    | 对    | No   |
| 24563-660 | 63HP | 175mm    | 2    | 对    | No   |
| 24563-661 | 63HP | 235mm    | 2    | 对    | No   |
| 24563-662 | 63HP | 275mm    | 2    | 对    | No   |
| 24563-663 | 63HP | 295mm    | 2    | 对    | No   |
| 24563-760 | 84HP | 175mm    | 2    | 对    | No   |
| 24563-761 | 84HP | 235mm    | 2    | 对    | No   |
| 24563-762 | 84HP | 275mm    | 2    | 对    | No   |
| 24563-763 | 84HP | 277.75mm | 2    | 对    | No   |

| 物料号       | 机架宽度 | 深度    | 包装数量 | 包装单位 | 快速发货 |
|-----------|------|-------|------|------|------|
| 24563-764 | 84HP | 295mm | 2    | 对    | No   |
| 24563-765 | 84HP | 355mm | 2    | 对    | No   |
| 24563-766 | 84HP | 415mm | 2    | 对    | No   |
| 24563-767 | 84HP | 495mm | 2    | 对    | No   |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

|                                                          |                                                          |                                                          |                                                          |
|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|
| <b>North America</b>                                     | <b>Europe</b>                                            | <b>Asia</b>                                              | <b>Middle East &amp; India</b>                           |
| All locations                                            | Straubenhardt, Germany                                   | Shanghai, China                                          | Dubai, United Arab Emirates                              |
| +1.763.422.2661                                          | +49.7082.794.0                                           | +86.21.2412.6943                                         |                                                          |
| Chat with us:                                            | Betschdorf, France                                       | Qingdao, China                                           | +971.4.378.1700                                          |
| <a href="http://nvent.com/schroff">nvent.com/schroff</a> | +33.3.88.90.64.90                                        | +86.532.8771.6101                                        | Bangalore, India                                         |
|                                                          | Warsaw, Poland                                           | Singapore                                                | +91.80.6715.2001                                         |
|                                                          | +48.22.209.98.35                                         | +65.6768.5800                                            | Istanbul, Turkey                                         |
|                                                          | Assago, Italy                                            | Shin-Yokohama, Japan                                     | +90.216.250.7374                                         |
|                                                          | +39.02.932.7141                                          | +81.45.476.0271                                          | Chat with us:                                            |
|                                                          | Chat with us:                                            | Chat with us:                                            | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |
|                                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |                                                          |



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE