

Varistar CP IP 20 机柜, 玻璃前门, 钢制后门



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

功能

防护类型 IP 20

带玻璃前门

带单点锁定的门, 带速卸锁扣的侧板

静态承载能力 1600 千克

技术参数

产品类型: 机柜

防护等级: IP20

材料: 钢

Table 1/3

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-040	42U	2000mm	暗灰色	600mm	RAL 7021	钢
10630-038	38U	1800mm	暗灰色	600mm	RAL 7021	钢

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-039	42U	2000mm	暗灰色	600mm	RAL 7021	钢
10630-037	38U	1800mm	暗灰色	600mm	RAL 7021	钢

Table 2/3						
物料号	深度	覆层颜色	包装数量	覆层颜色代码	符合	完成
10630-040	600mm	暗灰色	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	粉末涂层
10630-038	800mm	暗灰色	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	粉末涂层
10630-039	600mm	暗灰色	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	粉末涂层
10630-037	600mm	暗灰色	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	粉末涂层

Table 3/3			
物料号	框架材料	静态负载	快速发货
10630-040	钢	1600kg	No
10630-038	钢	1600kg	No
10630-039	钢	1600kg	No
10630-037	钢	1600kg	No

杆式把手可以添加到门上。

ServicePlus EMC 上提供了更多尺寸和版本。请单独订购基座/底座。如装配托盘和滑轨，需要另外订购一对角轨。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE