

Varistar CP Plain Steel Door, Seismic EMC and IP55, 多点锁定



EMC和IP55钢制门，带手柄和4点锁。

功能

带按钮的摇柄锁

开门角度 180°

带多点锁定的钢制门，适用于抗震和 EMC 应用

技术参数

产品类型: 机柜门

防护等级: IP55

材料: 钢

Table 1/2

物料号	机架高度	高度	宽度	包装数量	符合	完成
21630-760	33U	1600mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层
21630-761	33U	1600mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层

物料号	机架高度	高度	宽度	包装数量	符合	完成
21630-762	38U	1800mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层
21630-763	38U	1800mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层
21630-764	42U	2000mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层
21630-765	42U	2000mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层
21630-766	47U	2200mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层
21630-767	47U	2200mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	粉末涂层

Table 2/2

物料号	锁定类型	类型	搭配	快速发货
21630-760	4 点锁定	钢制门，平板	Varistar CP	No
21630-761	4 点锁定	钢制门，平板	Varistar CP	No
21630-762	4 点锁定	钢制门，平板	Varistar CP	No
21630-763	4 点锁定	钢制门，平板	Varistar CP	No
21630-764	4 点锁定	钢制门，平板	Varistar CP	No

物料号	锁定类型	类型	搭配	快速发货
21630-765	4 点锁定	钢制门，平板	Varistar CP	No
21630-766	5 点锁定	钢制门，平板	Varistar CP	No
21630-767	5 点锁定	钢制门，平板	Varistar CP	No

其他产品详情

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE