

Support Arm for Monitor

CONNECT AND PROTECT

For Electronics Cabinets in Test and Measurement

Modern support arm for mounting a flat screen monitor, keyboard and mouse in industrial or laboratory environments. Thanks to perfectly harmonized components, installation on your electronics cabinet can be installed by one person within a few minutes.



FEATURES AND BENEFITS

The support arm allows screen tilting with optional swivel and rotation functions for individual needs. The keyboard can be folded up to save space. Cable management within the wall duct is available as another space-saving measure.

Monitor arm for electronics cabinets

- **Super flexible:** Offers 12 inch vertical height adjustment
- **Easy mounting:** Simple installation on the side panel or frame
- **Maximum rotation:** Flat panel arm swivels 340 degrees at monitor end and 180 degrees at mounting end
- **Space-saving:** When folded up, the [arm/monitor] is only 5 inches from the side panel



Swivelling $\pm 90^\circ$

Cable Management

- Support for flat panel displays from 15" to 32"
- VESA adapter 75x75mm, 100x100mm
- Maximum weight: up to 10 kg
- Removable arm
- Panorama adjustment (90° on each side)
- Tilt: -20° to 90°
- Material: steel and aluminum
- Screw type: M4

Part Number: 60118-562



Swivelling $\pm 90^\circ$

Cable Management

- Arm for one monitor screen up to $\leq 24"$
- Maximum supported weight: 8 kg
- Adjustable: Tilt ($+5^\circ / 35^\circ$) 90° , 360° rotation
- Adjustable height: 124 mm
- Material, steel, plastic, aluminum
- VESA: 100x100 mm, 75x75 mm
- Supports keyboard and mouse
- Cable Management System

Part Number: 60118-563

MOUNTING KITS

Depending on the cabinet model (whether Varistar or Novastar), please order fixing kit separately.

Part Number: 25630-184 for Novastar cabinet

Part Number: 25630-185 for Varistar cabinet

NORTH AMERICA

All locations

Tel +1.800.525.4682

EUROPE

Straubenhardt, Germany

Tel +49.7082.794.0

Betschdorf, France

Tel +33.388.90.64.90

Warsaw, Poland

Tel +48.22.209.98.35

Assago, Italy

Tel +39.02.932.714.1

ASIA

Shanghai, P.R. China

Tel +86.21.2412.6943

Qingdao, P.R. China

Tel +86.523.8771.6101

Singapore

Tel +65.6768.5800

Shin-Yokohama, Japan

Tel +81.45.476.0271

MIDDLE EAST & INDIA

Dubai, United Arab Emirates

Tel +971.4.37.81.700

Bangalore, India

Tel +91.80.67152001

Istanbul, Turkey

Tel +90.216.250.7374



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER