

BD Two Pole Distribution Block, 40 A

Data Solutions



CERTIFIERINGAR



DESIGN

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Easily clips onto DIN rail or mounts to panel with screws

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

SPECIFIKATIONER

Katalognummer	BD-40A
Artikelnummer	563720



Katalognummer	BD-40A
Max. märkström, IEC	40A
Kortsiktig hållström (Icw) 1s	4.5kA
Maximal kortslutningsström (Ipk)	22kA
Max. arbetsspänning, IEC (Ui)	500
Antal anslutningar på ledningssida	2
Compact i flertrådsstorlek för ledningssida	6 - 16 mm ²
Flertrådsstorlek för ledningssida – hylsa	4 – 10mm ²
Antal anslutningar på belastningssida	15
Compact i flertrådsstorlek för belastningssida	(15) 1,5 - 4 mm ²
Flertrådsstorlek för belastningssida – hylsa	(15) 0,75 – 4 mm ²
Djup (D)	50mm
Höjd (H)	50mm
Bredd (W)	130mm
Enhetsvikt	0.22kg
Brandklassning	UL® 94V-0
Uppfyller	IEC® 60947-7-1

YTTERLIGARE PRODUKTINFORMATION

Line side and load side number of connections are per pole.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMS



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE