


# EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

## Energiföretag

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



## CERTIFIERING



## FUNKTIONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

## SPECIFIKATIONER

Table 1/3

| Katalognummer | Rack Height | Djup   | Package Quantity | For Mounting | Board Depth            | EMC Gasket Type |
|---------------|-------------|--------|------------------|--------------|------------------------|-----------------|
| 24563-172     | 3 U         | 235 mm | 1                | Backplane    | 160 mm, 220 mm         | Textile         |
| 24563-173     | 3 U         | 295 mm | 1                | Backplane    | 160 mm, 220 mm, 280 mm | Textile         |
| 24563-174     | 3 U         | 355 mm | 1                | Backplane    | 160 mm, 220 mm, 280 mm | Textile         |
| 24563-472     | 6 U         | 235 mm | 1                | Backplane    | 160 mm, 220 mm         | Textile         |
| 24563-473     | 6 U         | 295 mm | 1                | Backplane    | 160 mm, 220 mm, 280 mm | Textile         |
| 24563-474     | 6 U         | 355 mm | 1                | Backplane    | 160 mm, 220 mm, 280 mm | Textile         |

Table 2/3

| Katalognummer | Shock and Vibration Tolerance | Handle Included | Montering | Uppfyller kraven enligt | EMC Shielding | Product Type    |
|---------------|-------------------------------|-----------------|-----------|-------------------------|---------------|-----------------|
| 24563-172     | 5 g (force)                   | Nej             | Rack      | IEC 60297-3-103         | Ja            | Subrack/Chassis |
| 24563-173     | 5 g (force)                   | Nej             | Rack      | IEC 60297-3-103         | Ja            | Subrack/Chassis |
| 24563-174     | 5 g (force)                   | Nej             | Rack      | IEC 60297-3-103         | Ja            | Subrack/Chassis |
| 24563-472     | 5 g (force)                   | Nej             | Rack      | IEC 60297-3-103         | Ja            | Subrack/Chassis |
| 24563-473     | 5 g (force)                   | Nej             | Rack      | IEC 60297-3-103         | Ja            | Subrack/Chassis |
| 24563-474     | 5 g (force)                   | Nej             | Rack      | IEC 60297-3-103         | Ja            | Subrack/Chassis |

Table 3/3

| Katalognummer | Rack Width | Statisk belastning |
|---------------|------------|--------------------|
| 24563-172     | 84 HP      | 15 kgf             |
| 24563-173     | 84 HP      | 15 kgf             |

| Katalognummer | Rack Width | Statisk belastning |
|---------------|------------|--------------------|
| 24563-174     | 84 HP      | 15 kgf             |
| 24563-472     | 84 HP      | 15 kgf             |
| 24563-473     | 84 HP      | 15 kgf             |
| 24563-474     | 84 HP      | 15 kgf             |

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**