


Front Handle One-Piece, Width 12.2 mm

Power Utilities



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFIERINGAR



DESIGN

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFIKATIONER

Table 1/2

Katalognummer	Rackhöjd	Förpackningskvantitet	Handtagstyp	Färg	Material	Produktfamilj
10501-116	1 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-029	6 U	1	Rakt	Svart	Aluminium	EuropacPRO
10501-022	6 U	1	Vinklat handtag	Silver	Aluminium	EuropacPRO

Katalognummer	Rackhöjd	Förpackningskvantitet	Handtagstyp	Färg	Material	Produktfamilj
10501-008	6 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-007	5 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-016	2 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-006	4 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-021	4 U	1	Vinklat handtag	Silver	Aluminium	EuropacPRO
10501-005	3 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-018	4 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-025	2 U	1	Rakt	Svart	Aluminium	EuropacPRO
10501-026	3 U	1	Rakt	Svart	Aluminium	EuropacPRO
10501-020	3 U	1	Vinklat handtag	Silver	Aluminium	EuropacPRO
10501-027	4 U	1	Rakt	Svart	Aluminium	EuropacPRO
10501-004	2 U	1	Rakt	Silver	Aluminium	EuropacPRO
10501-028	5 U	1	Rakt	Svart	Aluminium	EuropacPRO

Table 2/2

Katalognummer	Produkttyp	Fungerar med.	Vridmoment
10501-116	Handtag	Underrack	
10501-029	Handtag	Underrack	2.4 N·m
10501-022	Handtag	Underrack	2.4 N·m
10501-008	Handtag	Underrack	2.4 N·m

Katalognummer	Produkttyp	Fungerar med.	Vridmoment
10501-007	Handtag	Underrack	
10501-016	Handtag	Underrack	
10501-006	Handtag	Underrack	
10501-021	Handtag	Underrack	2.4 N·m
10501-005	Handtag	Underrack	2.4 N·m
10501-018	Handtag	Underrack	2.4 N·m
10501-025	Handtag	Underrack	
10501-026	Handtag	Underrack	2.4 N·m
10501-020	Handtag	Underrack	2.4 N·m
10501-027	Handtag	Underrack	
10501-004	Handtag	Underrack	
10501-028	Handtag	Underrack	

YTTERLIGARE PRODUKTINFORMATION

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE