

# Varistar CP Perforated, Seismic Base Plate, EMC, for Rear Cable Ducting

## Energiföretag

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

### FUNKTIONER

Installation from outside

Cutout at rear

60 mm deep

Cable ducting with IP 55 / EMC gasket

### SPECIFIKATIONER

Table 1/2

| Katalognummer | Bredd  | Djup    | Färg       | Color Code | Uppfyller kraven enligt                     | Material |
|---------------|--------|---------|------------|------------|---------------------------------------------|----------|
| 20630-325     | 600 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |
| 20630-326     | 600 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |
| 20630-327     | 600 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |
| 20630-328     | 600 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |
| 20630-329     | 800 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |
| 20630-330     | 800 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |

| Katalognummer | Bredd  | Djup    | Färg       | Color Code | Uppfyller kraven enligt                     | Material |
|---------------|--------|---------|------------|------------|---------------------------------------------|----------|
| 20630-331     | 800 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |
| 20630-332     | 800 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Stål     |

Table 2/2

| Katalognummer | Product Type      | Typ                    | Fungerar med |
|---------------|-------------------|------------------------|--------------|
| 20630-325     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-326     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-327     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-328     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-329     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-330     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-331     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |
| 20630-332     | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP  |

## ADDITIONAL PRODUCT DETAILS

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

Please purchase the grounding kit separately.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**