

# Varistar CP Steel Door, Plain, Multi-Point Locking

## Energiföretag

EMC and IP55 Steel Door with lever handle and 4-Point locking.

### FUNKTIONER

Lever handle with push button

Opening angle 180°

Steel door with 4-point locking for EMC applications

### SPECIFIKATIONER

Table 1/2

| Katalognummer | Rack Height | Höjd    | Bredd  | Färg       | Color Code | Locking Type    |
|---------------|-------------|---------|--------|------------|------------|-----------------|
| 21630-521     | 24 U        | 1200 mm | 600 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-522     | 24 U        | 1200 mm | 800 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-523     | 29 U        | 1400 mm | 600 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-524     | 29 U        | 1400 mm | 800 mm | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-525     | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-526     | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-527     | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-528     | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | 4-Point Locking |

| Katalognummer | Rack Height | Höjd    | Bredd  | Färg       | Color Code | Locking Type    |
|---------------|-------------|---------|--------|------------|------------|-----------------|
| 21630-529     | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-530     | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-531     | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | 5-Point Locking |
| 21630-532     | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | 5-Point Locking |

Table 2/2

| Katalognummer | Product Type | Protection Rating |
|---------------|--------------|-------------------|
| 21630-521     | Cabinet Door | IP55              |
| 21630-522     | Cabinet Door | IP55              |
| 21630-523     | Cabinet Door | IP55              |
| 21630-524     | Cabinet Door | IP55              |
| 21630-525     | Cabinet Door | IP55              |
| 21630-526     | Cabinet Door | IP55              |
| 21630-527     | Cabinet Door | IP55              |
| 21630-528     | Cabinet Door | IP55              |
| 21630-529     | Cabinet Door | IP55              |
| 21630-530     | Cabinet Door | IP55              |
| 21630-531     | Cabinet Door | IP55              |
| 21630-532     | Cabinet Door | IP55              |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## VARNING

---

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**