



Horizontal Rail, Rear, Type L-VT, Light, 1000 mm

KATALOGNUMMER

34560-601



Combinations of horizontal rails and side panels

	A° = can be combined.	A° = combination: not recommended		
light = L		-	+	+
heavy = H		+	rework for double for connection	rework for heavy and connection for heavy
light + L		rework for light	rework for double	-
heavy + H		+	+	-
heavy + L		+	+	-
light + H		+	+	-
light = L		light = L	double = D	heavy = H
heavy = H		double = D	heavy = H	heavy = H
light = L		light = L	double = D	heavy = H
heavy = H		heavy = H	heavy = H	heavy = H

The horizontal rail, type VT enables the direct assembly of a backplane.

CERTIFIERINGAR



DESIGN

For direct backplane mounting

Recessed installation for low mechanical demands (L-VT)

Mounting top and bottom

Aluminum extrusion, anodized finish, conductive contact surface

PRODUKTATTRIBUT

Rackbredd: 195HP

Antal i förpackningen: 1

Yta: Anodiserad

Längd: 1000mm

Material: Aluminium

Produktfamilj: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Produkttyp: Horisontell skena

Typ: Lätt, VT

Fungerar med: Underrack; Lådor

YTTERLIGARE PRODUKTINFORMATION

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplikering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE