

nVent LENTON Interlok Grommet



The nVent LENTON Grommet is used in conjunction with the nVent LENTON Bolted Form Mount and nVent LENTON Toggle Form Mount. These Grommets are used to secure nVent LENTON Interlok Grout-Fill Coupler variants in repeatable locations in the formwork. Once a Grout-Fill Coupler is placed over a Grommet, the Form Mount bolt is tightened, which expands the outside diameter of the Grommet, thus holding the Grout-Fill Coupler in place.

功能

Color-coded for the appropriate coupler size

Durable and reusable

技术参数

材料: 聚酯尿烷

Table 1/2


物料号	订货号	直径 1 (Ø1)	直径 2 (Ø2)	长度 (L)	配合使用	颜色
LK307A	145811	46 mm	19 mm	52mm	LK5, LK6, LK7	蓝色
LK308A	145812	49 mm	19 mm	52mm	LK8	红色
LK316A		40 mm	19 mm	51mm	LK16	黑色
LK320A		43 mm	19 mm	51mm	LK20	黄色
LK309A	145813	52 mm	19 mm	52mm	LK9	黑色
LK310A	145814	57 mm	19 mm	52mm	LK10	黄色

物料号	订货号	直径 1 (Ø1)	直径 2 (Ø2)	长度 (L)	配合使用	颜色
LK311A	145815	60 mm	19 mm	52mm	LK11	蓝色
LK314A	145816	67 mm	19 mm	52mm	LK12, LK40, LKT14	红色
LK318A	145817	83 mm	19 mm	52mm	LKT18, LKT50	黑色

Table 2/2		
物料号	订货号	单位重量
LK307A	145811	0.08 kg
LK308A	145812	0.09 kg
LK316A		0.12 kg
LK320A		0.15 kg
LK309A	145813	0.11 kg
LK310A	145814	0.13 kg
LK311A	145815	0.15 kg
LK314A	145816	0.22 kg
LK318A	145817	0.5 kg

其他产品详情

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE