

T-Series Vertical Filler Material Kit



T-Series vertical filler material kits contain the following: Filler material, two vertical packings, pouring basin ceramic guide tube and pouring basin crucible ceramic and disk. All filler material kits contain one-time use components that are sized to a specific sleeve, pouring basin and pouring basin crucible combination. Ordering filler material kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

功能

Simplifies ordering

Used to splice the same diameter bars

All components are for one-time use

技术参数

Table 1/1

物料号	套管	钢筋尺寸，公制	钢筋尺寸，美国	钢筋尺寸，加拿大
RBT121018B	标准长度	38 mm	#12	
RBT4101B	标准长度	12 mm	#4	10M
RBT5101B	标准长度	16 mm	#5	15M
RBT6101B	标准长度	20 mm	#6	20M
RBT7101B	标准长度	22 mm	#7	
RBT81011B	加长长度	25 mm	#8	25M

物料号	套管	钢筋尺寸，公制	钢筋尺寸，美国	钢筋尺寸，加拿大
RBT8101B	标准长度	25 mm	#8	25M
RBT91011B	加长长度	28 mm	#9	30M
RBT9101B	标准长度	28 mm	#9	30M
RBT10911B	加长长度	32 mm	#10	
RBT1091B	标准长度	32 mm	#10	
RBT111011B	加长长度	36 mm	#11	35M
RBT11101B	标准长度	36 mm	#11	35M
RBT14101B	标准长度	43 mm	#14	45M
RBT1891B	标准长度	57 mm	#18	55M

其他产品详情


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Filler material kits are a component in splice kits. Care should be taken to avoid duplication of orders.

Components can also be purchased separately: (1) Filler Material, (2) Vertical Top Packing, (3) Vertical Bottom Packing, (4) Pouring Basin Ceramic Guide Tube, and (5) Crucible Ceramic and Disk.

Filler Material Kit Components				
Filler Material Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube
RBT4101B	RBF40	RBS354710 RBS354710	RBS5037	RBS5039
RBT5101B	RBF40	RBS354710 RBS35475	RBS5037	RBS5038
RBT6101B	RBF50	RBS35473.5 RBS35477	RBS5037	RBS5038
RBT7101B	RBF50	RBS35474 RBS35478	RBS5037	RBS5038
RBT81011B	RBF70	RBS354710 RBS35475	RBS5037	RBS5038
RBT8101B	RBF55	RBS354710 RBS35475	RBS5037	RBS5038
RBT91011B	RBF90	RBS354711 RBS35475.5	RBS5037	RBS5038
RBT9101B	RBF80	RBS354711 RBS35475.5	RBS5037	RBS5038
RBT10911B	RBF105	RBS354712 RBS35476	RBS5037	RBS5038
RBT1091B	RBF90	RBS354712 RBS35476	RBS5037	RBS5038
RBT111011B	RBF125	RBS354712 RBS35476	RBS5037	RBS5038
RBT11101B	RBF105	RBS354712 RBS35476	RBS5037	RBS5038
RBT121018B	RBF180	RBS354715 RBS35477	RBS5037	RBS5038
RBT14101B	RBF195	RBS354715 RBS35477	RBS5037	RBS5039
RBT1891B	RBF270	RBS354720 RBS35479	RBS5037	RBS5039

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE