

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base

Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

认证



功能

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

Table 1/2						
物料号	机架高度	深度	可用宽度	安装	符合	EMC 屏蔽
20860-601	1 U	220 mm	403 mm	机架	IEC 60297-3-100, IEC 60297-3-105	无（可改装）
20860-602	1 U	280 mm	403 mm	机架	IEC 60297-3-100, IEC 60297-3-105	无（可改装）
20860-603	1 U	340 mm	4 mm	机架	IEC 60297-3-100	无（可改装）
20860-604	2 U	220 mm	4 mm	机架	IEC 60297-3-100	无（可改装）
20860-605	2 U	280 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-606	2 U	340 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-607	3 U	280 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-608	3 U	340 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-609	3 U	400 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-610	3 U	460 mm	4 mm	机架	IEC 60297-3-100	无（可改装）
20860-611	4 U	280 mm	4 mm	机架	IEC 60297-3-100	无（可改装）
20860-612	4 U	340 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-613	4 U	400 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-614	4 U	460 mm	403 mm	机架	IEC 60297-3-100	无（可改装）
20860-615	5 U	460 mm	403 mm	机架	IEC 60297-3-100	无（可改装）

Table 2/2

物料号	产品系列	产品类型	类型	认证
20860-601	MultipacPRO	插箱/机箱	实心	RoHS
20860-602	MultipacPRO	插箱/机箱	实心	RoHS
20860-603	MultipacPRO	插箱/机箱	实心	
20860-604	MultipacPRO	插箱/机箱	实心	
20860-605	MultipacPRO	插箱/机箱	实心	RoHS
20860-606	MultipacPRO	插箱/机箱	实心	RoHS
20860-607	MultipacPRO	插箱/机箱	实心	RoHS
20860-608	MultipacPRO	插箱/机箱	实心	RoHS
20860-609	MultipacPRO	插箱/机箱	实心	RoHS
20860-610	MultipacPRO	插箱/机箱	实心	
20860-611	MultipacPRO	插箱/机箱	实心	
20860-612	MultipacPRO	插箱/机箱	实心	RoHS
20860-613	MultipacPRO	插箱/机箱	实心	RoHS
20860-614	MultipacPRO	插箱/机箱	实心	RoHS
20860-615	MultipacPRO	插箱/机箱	实心	RoHS

其他产品详情

Please order front handles separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE