

19" 带把手安装孔的前面板

使用 SCHROFF 19" 前面板定义设备前面和侧面。SCHROFF 19" 带有额外的把手安装孔，尺寸为 1 U 至 6 U。



认证



功能

19" 前面板有用于安装把手的开孔

技术参数

机架宽度: 95HP
材料: 铝
附件类型: 前面板
产品类型: 前面板

Table 1/3

物料号	机架高度	深度 (D)	手柄类型	完成	安装	包装数量
30219-161	1U	3mm	前把手	阳极氧化	正面螺钉安装	1
40304-050	1U	3mm	前把手	阳极氧化	正面螺钉安装	1


物料号	机架高度	深度 (D)	手柄类型	完成	安装	包装数量
30219-162	2U	3mm	前把手	阳极氧化	正面螺钉安装	1
40304-051	2U	3mm	前把手	阳极氧化	正面螺钉安装	1
30219-163	3U	3mm	前把手	阳极氧化	正面螺钉安装	1
30219-164	4U	3mm	前把手	阳极氧化	正面螺钉安装	1
40304-052	3U	3mm	前把手	阳极氧化	正面螺钉安装	1
30219-165	5U	3mm	前把手	阳极氧化	正面螺钉安装	1
40304-053	4U	3mm	前把手	阳极氧化	正面螺钉安装	1
30219-166	6U		前把手	阳极氧化	正面螺钉安装	1
40304-054	5U	3mm	前把手	阳极氧化	正面螺钉安装	1
40304-055	6U	3mm	前把手	阳极氧化	正面螺钉安装	1

Table 2/3						
物料号	正面表面处理	反面表面处理	边缘处理	EMC 屏蔽	高度 (H)	类型
30219-161	阳极氧化	阳极氧化	否	否	43.6mm	19" 前面板
40304-050	阳极氧化	阳极氧化	是	否	43.6mm	19" 前面板
30219-162	阳极氧化	阳极氧化	否	否	88.1mm	19" 前面板
40304-051	阳极氧化	阳极氧化	是	否	88.1mm	19" 前面板
30219-163	阳极氧化	阳极氧化	否	否	132.5mm	19" 前面板

物料号	正面表面处理	反面表面处理	边缘处理	EMC 屏蔽	高度 (H)	类型
30219-164	阳极氧化	阳极氧化	否	否	177mm	19" 前面板
40304-052	阳极氧化	阳极氧化	是	否	132.5mm	19" 前面板
30219-165	阳极氧化	阳极氧化	否	否	221.4mm	19" 前面板
40304-053	阳极氧化	阳极氧化	是	否	177mm	19" 前面板
30219-166	阳极氧化	阳极氧化	否	否	265.9mm	19" 前面板
40304-054	阳极氧化	阳极氧化	是	否	221.4mm	19" 前面板
40304-055	阳极氧化	阳极氧化	是	否	265.9mm	19" 前面板

Table 3/3		
物料号	宽度 (W)	快速发货
30219-161	483mm	No
40304-050	483mm	No
30219-162	483mm	No
40304-051	483mm	No
30219-163	483mm	No
30219-164	483mm	No
40304-052	483mm	No
30219-165	483mm	No

物料号	宽度 (W)	快速发货
40304-053	483mm	No
30219-166	483mm	No
40304-054	483mm	No
40304-055	483mm	No



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE