


DIN 轨道

DIN

轨道是一种标准金属轨道，适合在设备机架内安装断路器和工业控制设备。



功能

预切割长度，开孔

钢，带电镀锌层

符合：EN 60715 标准

技术参数

产品类型: DIN 轨道

Table 1/2

物料号	材料	高度	长度	完成	包装数量	深度
20118-878	钢	35mm	125mm	镀锌	4	7.5mm
20118-879	钢	35mm	175mm	镀锌	4	7.5mm
20118-872	钢	35mm	125mm	镀锌	4	15mm
20118-880	钢	35mm	275mm	镀锌	4	7.5mm
20118-890	钢	35mm	125mm	镀锌	10	7.5mm

物料号	材料	高度	长度	完成	包装数量	深度
20118-873	钢	35mm	175mm	镀锌	4	15mm
20118-881	钢	35mm	375mm	镀锌	4	7.5mm
20118-891	钢	35mm	175mm	镀锌	10	7.5mm
20118-882	钢	35mm	475mm	镀锌	4	7.5mm
20118-874	钢	35mm	275mm	镀锌	4	15mm
20118-884	钢	35mm	125mm	镀锌	10	15mm
20118-883	钢	35mm	575mm	镀锌	4	7.5mm
20118-892	钢	35mm	275mm	镀锌	10	7.5mm
20118-875	钢	35mm	375mm	镀锌	4	15mm
20118-885	钢	35mm	175mm	镀锌	10	15mm
20118-876	钢	35mm	475mm	镀锌	4	15mm
20118-893	钢	35mm	375mm	镀锌	10	7.5mm
20118-877	钢	35mm	575mm	镀锌	4	15mm
20118-894	钢	35mm	475mm	镀锌	10	7.5mm
20118-886	钢	35mm	275mm	镀锌	10	15mm
20118-895	钢	35mm	575mm	镀锌	10	7.5mm
20118-887	钢	35mm	375mm	镀锌	10	15mm

物料号	材料	高度	长度	完成	包装数量	深度
20118-888	钢	35mm	475mm	镀锌	10	15mm
20118-889	钢	35mm	575mm	镀锌	10	15mm

Table 2/2		
物料号	宽度	快速发货
20118-878	125mm	No
20118-879	175mm	No
20118-872	125mm	No
20118-880	275mm	No
20118-890	125mm	No
20118-873	175mm	No
20118-881	375mm	No
20118-891	175mm	No
20118-882	475mm	No
20118-874	275mm	No
20118-884	125mm	No
20118-883	575mm	No
20118-892	275mm	No

物料号	宽度	快速发货
20118-875	375mm	No
20118-885	175mm	No
20118-876	475mm	No
20118-893	375mm	No
20118-877	575mm	No
20118-894	475mm	No
20118-886	275mm	No
20118-895	575mm	No
20118-887	375mm	No
20118-888	475mm	No
20118-889	575mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE