

PXI Express 控制器, 4 HP, I3-1115G4E 16-512

物料号

21265-120



The nVent SCHROFF PXIe embedded controller is the most compact and powerful 3U one-slot embedded controller for the PXI Express and CPCIexp platforms. With its huge and future-ready interface capabilities, it runs perfectly with most test and measurement applications. The Controller is driven by a 11th generation Intel® Core™ i3 / i5 processors combined with up to 64GB DDR4 memory and easily supports high bandwidth applications with future ready PCIe Gen4 and dual 2500BASE-T system interconnectivity.

功能

PXI Express 系统控制器, 3 U, 4 HP, 采用 Intel Core I3-1115G4E 处理器

PXI™-5 PXI Express 硬件规格符合修订版 2.0 标准

最高 14 GB/s PCIe 带宽

可升级 m.2 NVMe 和 DDR4 存储

3x USB3.1, 前面板上 2x GbE 和 1x DP 1.2

完全可定制的 AMI Aptio® 嵌入式 BIOS

产品属性

产品类型: 系统

类型: 控制器

数据传输: PCIe Gen3

机架高度: 3U

符合: PXISA PXI-5 R1.1

深度: 160mm

Gross Weight: 0.548kg

包装数量: 1

其他产品详情

符合 PICMG 修订版 3.0 和 PXI-5。

可应要求提供改装的控制器。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE