

LE260 系列手柄制动 Card-Lok

物料号

LE260-4.80TM2-2



The Series LE260 features a tool-free lever design, ideal for field level maintenance, as well as an integrated extraction providing a 4:1 mechanical advantage.

可应要求在发货前预先校准夹持力。

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

认证



功能

长度 96.5 毫米 (3.80 英寸) 至 325 毫米 (12.80 英寸) , 12.7 毫米 (0.5 英寸) 增量

集成助拔器

5 段, 长杆设计

手柄制动

重量 1.17 克/厘米 (0.105 盎司/英寸)

灵活的安装选项

最小延展: 8.26 mm (0.325")

外形尺寸: 6.35 mm (0.250") x 6.26 mm (0.270")

仅提供黑色阳极氧化镀层款式

可用于冷板

平均夹持力 = 预先校准为 125 lbs 或 145 lbs, 客户指定

产品属性

产品类型: PCB 固定器

材料: 铝

类型: 轴式

热性能: 良好

型材: 6.35 x 6.26 mm

夹持力: 45 – 90kgf

间隙宽度: PCB + (7.0 - 7.9 mm)

其他产品详情

nVent

可能会不定期修改其产品技术参数以符合适用的工业、军用或其他相关标准。除非另有书面协定，否则已取消或被取代的军用规格将被最新规格替代并完成认证。无论您是否已获得此类修改的通知，即使不同于原始技术参数或客户引用的技术参数，符合此类（最新或替代）技术参数的产品将被视为完全符合要求的合格产品。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE