


EuropacPRO Advanced EMC 45 Top and Bottom Covers, Screwed to Side Panel, Ø 2.3mm



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

认证



功能

Top and bottom covers with EMC and airflow optimized perforation, fulfills the requirements of the fire safety standard EN 62368-1, perforation diameter Ø 2.3mm, degree 50%

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Cover plate for bolting to the side panel

Suitable for use with all horizontal rails, besides Rugged

技术参数

材料:	铝
产品类型:	盖板
产品系列:	EuropacPRO
完成:	钝化

类型: 穿孔
搭配: 插箱

Table 1/1

物料号	机架宽度	深度	包装数量	包装单位	快速发货
24563-555	36HP	175mm	2	对	No
24563-556	36HP	235mm	2	对	No
24563-560	42HP	175mm	2	对	No
24563-561	42HP	235mm	2	对	No
24563-562	42HP	275mm	2	对	No
24563-563	42HP	277.75mm	2	对	No
24563-564	42HP	295mm	2	对	No
24563-660	63HP	175mm	2	对	No
24563-661	63HP	235mm	2	对	No
24563-662	63HP	275mm	2	对	No
24563-663	63HP	295mm	2	对	No
24563-760	84HP	175mm	2	对	No
24563-761	84HP	235mm	2	对	No
24563-762	84HP	275mm	2	对	No
24563-763	84HP	277.75mm	2	对	No

物料号	机架宽度	深度	包装数量	包装单位	快速发货
24563-764	84HP	295mm	2	对	No
24563-765	84HP	355mm	2	对	No
24563-766	84HP	415mm	2	对	No
24563-767	84HP	495mm	2	对	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE