


# EuropacPRO EMC 屏蔽套件, 水平轨道之间



接触条可使水平轨道之间发生接触。如果两个水平轨道上下重叠安装，密封件及金属条可实现 EMC 屏蔽。

## 认证



## 功能

如果两个水平轨道上下重叠安装, 密封件及金属条可实现 EMC 屏蔽

## 技术参数

材料: 不锈钢; 铝  
 产品系列: EuropacPRO  
 产品类型: 屏蔽套件  
 搭配: 插箱

Table 1/1

| 物料号       | 机架宽度 | 包装数量 | 长度    | 快速发货 |
|-----------|------|------|-------|------|
| 24562-520 | 20HP | 1    | 107mm | No   |
| 24562-528 | 28HP | 1    | 147mm | No   |

| 物料号       | 机架宽度 | 包装数量 | 长度    | 快速发货 |
|-----------|------|------|-------|------|
| 24562-540 | 40HP | 1    | 208mm | No   |
| 24562-542 | 42HP | 1    | 218mm | No   |
| 24562-584 | 84HP | 1    | 431mm | No   |
| 24562-563 | 63HP | 1    | 325mm | No   |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE