

Plain Front Panels For Power Distribution, MSMBP



This mild steel plain front panel, MSMBP, is for the front frame of a fix system or modular frames. It can be machined easily and used for mounting of components and equipment, and also serve as a cover.

功能

Description: Plain front panel for modular assemblies. It has a top and bottom bending to provide extra rigidity.

Material: 1.25 mm steel.

Finish: RAL 7035 structured powder coating.

Delivery: 1 piece with mounting material.

Mounting requirements: To be assembled on the modular system frame.

技术参数

颜色：浅灰色

材料：低碳钢

完成：粉末涂层

颜色代码：RAL 7035

Table 1/1						
物料号	高度	宽度	深度	外壳材料	产品系列	面板尺寸
MSMBP5006R5	500mm	600mm	13mm	低碳钢	独立, 壁挂式安装	499 x 503mm
MSMBP4008R5	400mm	800mm	13mm	低碳钢	独立, 壁挂式安装	399 x 703mm
MSMBP4006R5	400mm	600mm	13mm	低碳钢	独立, 壁挂式安装	399 x 503mm
MSMBP0508R5	50mm	800mm	13mm	低碳钢	独立, 壁挂式安装	49 x 703mm
MSMBP5008R5	500mm	800mm	13mm	低碳钢	独立, 壁挂式安装	499 x 703mm
MSMBP1008R5	100mm	800mm	13mm	低碳钢	独立, 壁挂式安装	99 x 703mm
MSMBP3008R5	300mm	800mm	13mm	低碳钢	独立, 壁挂式安装	299 x 703mm
MSMBP4506R5	450mm	600mm	13mm	低碳钢	独立, 壁挂式安装	449 x 503mm
MSMBP1506R5	150mm	600mm	13mm	低碳钢	独立, 壁挂式安装	149 x 503mm
MSMBP3006R5	300mm	600mm	13mm	低碳钢	独立, 壁挂式安装	299 x 503mm
MSMBP6006R5	600mm	600mm	13mm	低碳钢	独立, 壁挂式安装	599 x 503mm
MSMBP4508R5	450mm	800mm	13mm	低碳钢	独立, 壁挂式安装	449 x 703mm
MSMBP2508R5	250mm	800mm	13mm	低碳钢	独立, 壁挂式安装	249 x 703mm
MSMBP1508R5	150mm	800mm	13mm	低碳钢	独立, 壁挂式安装	149 x 703mm
MSMBP6008R5	600mm	800mm	13mm	低碳钢	独立, 壁挂式安装	599 x 703mm

物料号	高度	宽度	深度	外壳材料	产品系列	面板尺寸
MSMBP2506R5	250mm	600mm	13mm	低碳钢	独立, 壁挂式安装	249 x 503mm
MSMBP0506R5	50mm	600mm	13mm	低碳钢	独立, 壁挂式安装	49 x 503mm
MSMBP2008R5	200mm	800mm	13mm	低碳钢	独立, 壁挂式安装	199 x 703mm
MSMBP2006R5	200mm	600mm	13mm	低碳钢	独立, 壁挂式安装	199 x 503mm
MSMBP1006R5	100mm	600mm	13mm	低碳钢	独立, 壁挂式安装	99 x 503mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE