

B-Series Vertical Sleeve



The B-Series Vertical Sleeve is designed to be welded perpendicularly to common grades of structural plates and shapes. Typical applications include welding to base plates, anchor plates and for tying together structural steel members.

功能

Designed to connect vertical reinforcing bars and angular reinforcing bars greater than 45 degrees

Machined from weldable grades of steel

Works with saw cut, flame cut and sheared bars

Can be visually inspected after installation

Available with extended sleeve lengths

技术参数

完成: 普通
 套管: 标准长度
 材料: 钢
 100% 美国国内内容: 是

Table 1/2

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	直径 1 (Ø1)	直径 2 (Ø2)	长度 1 (L1)
RBB592JA	16 mm	#5	15M	35 mm	22 mm	127 mm
RBB692JA	20 mm	#6	20M	38 mm	25 mm	127 mm

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	直径 1 (Ø1)	直径 2 (Ø2)	长度 1 (L1)
RBB792JA	22 mm	#7		41 mm	29 mm	127 mm
RBB8101JA	25 mm	#8	25M	48 mm	32 mm	127 mm
RBB992JA	28 mm	#9	30M	54 mm	38 mm	127 mm
RBB1092JA	32 mm	#10		57 mm	41 mm	127 mm
RBB11101JA	36 mm	#11	35M	64 mm	44 mm	152 mm
RBB1292JA	38 mm	#12		70 mm	48 mm	152 mm
RBB14101JA	43 mm	#14	45M	76 mm	54 mm	152 mm
RBB1892JA	57 mm	#18	55M	95 mm	67 mm	178 mm

Table 2/2		
物料号	长度 2 (L2)	单位重量
RBB592JA	64 mm	0.54 kg
RBB692JA	64 mm	0.64 kg
RBB792JA	64 mm	0.68 kg
RBB8101JA	64 mm	1 kg
RBB992JA	64 mm	1.13 kg
RBB1092JA	64 mm	1.22 kg
RBB11101JA	76 mm	1.91 kg


物料号	长度 2 (L2)	单位重量
RBB1292JA	64 mm	2.27 kg
RBB14101JA	64 mm	2.72 kg
RBB1892JA	64 mm	5.03 kg

其他产品详情

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE