

T-Series Horizontal Splice Kit, Side Fill



T-Series splice kits contain the following: Sleeve, filler material kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), pouring basin and pouring basin crucible. Splice kits are ordered based on the quantity of splices needed. Sleeves and filler material kits are one-time use parts. Pouring basins and crucibles are prorated based on their anticipated life. Ordering splice kits simplifies ordering, reduces order errors and helps ensure proper sizing of components. Kits can be ordered with longer (extended) sleeves for use when the reinforcing steel deformation pattern or spacing does not meet the minimum product specifications.

功能

Simplifies ordering

Used to splice the same diameter bars

技术参数

套管： 标准长度

Table 1/2

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	长度 1 (L1)	长度 2 (L2)	高度 [1] (H1)
RBT8101HS	25 mm	#8	25M	84 mm	403 mm	464mm
RBT1891HS	57 mm	#18	55M	102 mm	423 mm	533mm
RBT11101HS	36 mm	#11	35M	94 mm	413 mm	502mm
RBT1091HS	32 mm	#10		88 mm	407 mm	502mm

物料号	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	长度 1 (L1)	长度 2 (L2)	高度 [1] (H1)
RBT6101HS	20 mm	#6	20M	84 mm	397 mm	464mm
RBT9101HS	28 mm	#9	30M	88 mm	407 mm	464mm

Table 2/2		
物料号	高度 [2] (H2)	直径 (Ø)
RBT8101HS	75mm	102 mm
RBT1891HS	75mm	178 mm
RBT11101HS	75mm	127 mm
RBT1091HS	75mm	127 mm
RBT6101HS	75mm	102 mm
RBT9101HS	75mm	102 mm

其他产品详情


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

All dimensions are for reference only.

Components can also be purchased separately: (1) Sleeve, (2) Filler Material Kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), (3) Pouring Basin, and (4) Pouring Basin Crucible.

Splice Kit Components							
Splice Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube	Sleeve	Pouring Basin	Pouring Basin Crucible
RBT6101 HS	RBF50	RBS35477	RBS5037	RBS5038	RBT6101H SA	RBWS154 7X	RBWS22774
RBT8101 HS	RBF55	RBS354710	RBS5037	RBS5038	RBT8101H SA	RBWS154 7C	RBWS22774
RBT9101 HS	RBF80	RBS354711	RBS5037	RBS5038	RBT9101H SA	RBWS154 7D	RBWS22774
RBT1091 HS	RBF90	RBS354712	RBS5037	RBS5038	RBT1091H SA	RBWS154 7E	RBWS22775
RBT1110 1HS	RBF105	RBS354712	RBS5037	RBS5038	RBT11101 HSA	RBWS154 7F	RBWS22775
RBT1891 HS	RBF270	RBS354720	RBS5037	RBS5039	RBT1891H SA	RBWS154 7M	RBWS22777

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE