

700 插入器/助拔器

物料号

A700-1



用于插入和拔出兼容 IEEE 1101.2、VITA 30.1、VITA 46.0 和 VITA 48.2 的传导冷却组件模块。

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

认证



功能

4.5:1 机械优势

提供插入助力和拉拔助力

专为传导冷却机箱应用而设计

用铝制成

产品属性

产品类型: PCB 助插器/助拔器

带 PIN: 否

材料: 铝

nVent

可能会不定期修改其产品技术参数以符合适用的工业、军用或其他相关标准。除非另有书面协定，否则已取消或被取代的军用规格将被最新规格替代并完成认证。无论您是否已获得此类修改的通知，即使不同于原始技术参数或客户引用的技术参数，符合此类（最新或替代）技术参数的产品将被视为完全符合要求的合格产品。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE