


Varistar CP Raised Top Cover



Fan top cover for better ventilation and active cooling.

功能

Uses same lifting eyes as normal top cover

技术参数

产品类型: 机柜/机架顶盖

防护等级: IP20

材料: 钢

Table 1/2

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
21630-583	600mm	300mm	1	暗灰色	RAL 7021	粉末涂层
21630-584	600mm	600mm	1	暗灰色	RAL 7021	粉末涂层
21630-585	600mm	800mm	1	暗灰色	RAL 7021	粉末涂层
21630-586	600mm	900mm	1	暗灰色	RAL 7021	粉末涂层
21630-587	600mm	1000mm	1	暗灰色	RAL 7021	粉末涂层

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
21630-588	600mm	1100mm	1	暗灰色	RAL 7021	粉末涂层
21630-589	600mm	1200mm	1	暗灰色	RAL 7021	粉末涂层
21630-590	800mm	600mm	1	暗灰色	RAL 7021	粉末涂层
21630-591	800mm	800mm	1	暗灰色	RAL 7021	粉末涂层
21630-592	800mm	900mm	1	暗灰色	RAL 7021	粉末涂层
21630-593	800mm	1000mm	1	暗灰色	RAL 7021	粉末涂层
21630-594	800mm	1100mm	1	暗灰色	RAL 7021	粉末涂层
21630-595	800mm	1200mm	1	暗灰色	RAL 7021	粉末涂层

Table 2/2	
物料号	快速发货
21630-583	No
21630-584	No
21630-585	No
21630-586	No
21630-587	No
21630-588	No
21630-589	No

物料号	快速发货
21630-590	No
21630-591	No
21630-592	No
21630-593	No
21630-594	No
21630-595	No

其他产品详情

Please purchase the grounding kit separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE