


Varistar CP Seismic Base Plate, IP55 and EMC, 单件

底板结构坚固，可覆盖机柜底板。



功能

底板坚固，覆盖在机柜的底座上

从外部装配

技术参数

产品类型: 机柜/机架底座

完成: 热浸镀锌

防护等级: IP55

材料: 钢

Table 1/2

物料号	宽度	深度	包装数量	符合	类型	搭配
20630-309	600mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP
20630-310	600mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP

物料号	宽度	深度	包装数量	符合	类型	搭配
20630-311	600mm	1000mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP
20630-312	600mm	1200mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP
20630-313	800mm	600mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP
20630-314	800mm	800mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP
20630-315	800mm	1000mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP
20630-316	800mm	1200mm	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	底板, 平板	Varistar CP

Table 2/2

物料号	快速发货
20630-309	No
20630-310	No
20630-311	No
20630-312	No
20630-313	No

物料号	快速发货
20630-314	No
20630-315	No
20630-316	No

其他产品详情

本底板用于不需要底部电缆入口的应用。

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE