


Varistar CP Seismic Base Plate, IP55, 单件

底板结构坚固，可覆盖机柜底板。



功能

底板坚固，覆盖在机柜的底座上

从外部装配

技术参数

产品类型： 机柜/机架底座

防护等级： IP55

材料： 钢

Table 1/2

物料号	宽度	深度	包装数量	颜色	颜色代码	符合
20630-301	600mm	600mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-302	600mm	800mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-303	1000mm	1000mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

物料号	宽度	深度	包装数量	颜色	颜色代码	符合
20630-304	600mm	1200mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-305	800mm	600mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-306	800mm	800mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-307	800mm	1000mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-308	1200mm	1200mm	1	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Table 2/2

物料号	完成	类型	搭配	快速发货
20630-301	粉末涂层	底板, 平板	Varistar CP	No
20630-302	粉末涂层	底板, 平板	Varistar CP	No
20630-303	粉末涂层	底板, 平板	Varistar CP	No
20630-304	粉末涂层	底板, 平板	Varistar CP	No
20630-305	粉末涂层	底板, 平板	Varistar CP	No
20630-306	粉末涂层	底板, 平板	Varistar CP	No
20630-307	粉末涂层	底板, 平板	Varistar CP	No
20630-308	粉末涂层	底板, 平板	Varistar CP	No

其他产品详情

本底板用于不需要底部电缆入口的应用。

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE