

Enlogic Input Metered, Outlet Switched PDU EN2 Series

Data Solutions



The Advantage Series Input Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

VLASTNOSTI

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information

UL 2900-1 certified for safety software cybersecurity for network-connectable products

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs. Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

SPECIFIKACE

Table 1/6

Katalogové číslo	Produktová řada	Typ	Product Type	Typ zásuvky	Socket Quantity	Barva
------------------	-----------------	-----	--------------	-------------	-----------------	-------

EN2951	Enlogic	Intelligent PDU	Socket Strip	(21) C13/C15, (21) C13/C15/C19/C 21	42	Black
EN2990	Enlogic	Intelligent PDU	Socket Strip	(24) Locking C13/C15, (24) Locking C13/C15/C19/C 21	48	Black

Table 2/6

Katalogové číslo	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Interrupt Rating
EN2951	Yes	1800mm	20 A, 2-pole, Hy-MagA	14.4 kVA	6	5kAIC
EN2990	Yes	1800mm	20 A, 1-pole, Hy-MagA	57.6 kVA North America, 69 kVA International	24	

Table 3/6

Katalogové číslo	Input Voltage	Phase	Nominal Power Output	Nominální napětí	Number of Output Voltages	Počet fází
EN2951	208V	3 PH Delta	208VAC	208V	42	3
EN2990			230VAC	415V		

Table 4/6

Katalogové číslo	On/Off Switch Included	Amperage (Derated Amperage)	Output Voltage	Rack Units	Plug Type	Metering Type
EN2951	Yes	50 A (40 A)	208VAC	0U	CS8365	Input
EN2990	Yes	100 A (80 A) North America, 100 A International	208 – 230VAC	0U	IEC 60309 5125P6W (IP67)	Input

Table 5/6

Katalogové číslo	Removable Input Cable	Materiál	Povrchová úprava	Výška	Šířka	Hloubka
EN2951	No	Ocel	Strukturovaný Práškový	1826mm	56mm	75mm

Katalogové číslo	Removable Input Cable	Materiál	Povrchová úprava	Výška	Šířka	Hloubka
EN2990	No	Ocel	Strukturovaný Práškový	2030mm	85mm	85mm

Table 6/6

Katalogové číslo	Hmotnost	Množství v balení	Input Cable Length
EN2951	13kg	1	1.8m
EN2990		1	1.8m

DALŠÍ PODROBNOSTI O PRODUKTU

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE