

nVent ERIFLEX Flexbus HCBC Plate with PE Connection

Data Solutions



CERTIFICATIONS



VLASTNOSTI

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows Flexbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

SPECIFIKACE

Materiál: Copper

Povrchová úprava: Tinned

Table 1/2

Katalogové číslo	Article Number	A	B	C	D	E
FLEXPLATE100 PE	508183	115mm	100mm	45mm	51mm	70mm
FLEXPLATE50PE	508182	65mm	100mm	45mm	41mm	70mm


Table 2/2

Katalogové číslo	Article Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Thickness (T)	Conductor Size	Unit Weight
FLEXPLATE100 PE	508183	12.5mm	18.5mm	5mm	960 mm ² , 1280 mm ² , 1810 mm ²	0.71kg
FLEXPLATE50PE	508182	10.5mm	14.5mm	5mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²	0.49kg

DALŠÍ PODROBNOSTI O PRODUKTU

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE