

RackChiller In-Row 45

Data Solutions



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. The RackChiller In-Row 45 air-to liquid cooler is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure. The units can be scaled optimally to suit individual packaging density and redundancy requirements.

The cooling system is integrated into a Varistar CP mobile frame for ideal side by side connection to Varistar CP or third party racks. The cooler comes with perforated front and rear doors. This allows seamless integration into rows of racks with hot or cold aisle containment. The integrated fans move the warm exhaust air from the hot aisle through an air to water heat exchanger where the heat is transferred to a water circuit. The air is then provided into the cold aisle towards the equipment.

VLASTNOSTI

In-Row air/liquid cooler, ideal for hot aisle containment

Hot-swappable components simplify repair and maximize availability

Designed for efficient operation at increased facility water temperatures

Combination with direct to chip liquid cooling

Modular standard - easy to adapt to individual requirements.

Minimum changes between In-Row and LHX+ (In-Rack) design - simplifies planning, layout and specification

Fans, power supplies, controller and control valve all are hot-swappable

Automatic fan speed and valve opening control

7" high resolution touch screen interface

Hydraulic and electric connection through top or bottom

Monitoring via Ethernet interface (Web browser, Modbus TCP, SNMP v2c) and Modbus RTU

SPECIFIKACE

Table 1/2									
Katalogové číslo	Product Type	Produktová řada	Šířka	Hloubka	Výška	Supply Voltage			
10630-103	Air/Liquid Heat Exchanger	RackChiller	300mm	1200mm	2000mm	200 – 240V			
10630-102	Air/Liquid Heat Exchanger	RackChiller	300mm	1000mm	2000mm	200 – 240V			

Table 2/2									
Katalogové číslo	Coolant Feed	Povrchová úprava	Materiál	Množství v balení	Stupeň krytí	Rack Height			
10630-103	Top, Bottom	Strukturovaný Práškový	Ocel	1	IP20	42U			
10630-102	Тор	Strukturovaný Práškový	Ocel	1	IP20	42U			

DALŠÍ PODROBNOSTI O PRODUKTU

For trouble-free operation of the air/liquid heat exchanger the quality requirements of the coolant must be maintained; The selection of appropriate anti-corrosion and frost protection agents depends on the environment in which the unit is used and on the external chiller

At coolant temperatures below 14 °C, there is an increased risk of condensation. We recommend using a condensate management package

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE