

Arc Weldable Bond



VLASTNOSTI

19-strand concentric cable flash-welded to steel rod for a bonding connection to structural steel and to rebar

Economical alternative to exothermic welding when only a few connections need to be made and an arc welder is available on site

Rod is sized to match the ampacity of the cable for fault currents

SPECIFIKACE

Table 1/1

Katalogové číslo	Materiál	Conductor Size	Cable Length	Rod Size	Rod Length
EWB2Q344	Copper, Ocel	4/0 Stranded	1.2m	19.1mm	203mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE