


# Cable to Ground Rod or Other Rounds, Rail



nVent ERICO Cadweld applications for railway properties utilize the nVent ERICO Cadweld Plus F80 and the nVent ERICO Cadweld F80 welding material alloys. nVent ERICO Cadweld exothermically welded connections are engineered to provide a permanent, molecular bond that will not loosen or corrode, enabling connection of dissimilar materials. The connections are designed to perform for the life of the conductor and/or installation. The nVent ERICO Cadweld connection has a current carrying capacity equal to or greater than that of the conductor and will withstand repeated fault currents without failing during operation. Once completed, installers can clearly ensure quality by visually inspecting the new connection.

## DIAGRAMS



## VLASTNOSTI

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

## SPECIFIKACE

Table 1/1

| Katalogové číslo | Mold Family | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual | Conductor Size | Conductor Outer Diameter, Nominal |
|------------------|-------------|-----------------|------------------------------|-----------------------------|----------------|-----------------------------------|
| PB10GR181E       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #8 Concentric  | 3.71mm                            |

| Katalogové číslo | Mold Family | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual | Conductor Size | Conductor Outer Diameter, Nominal |
|------------------|-------------|-----------------|------------------------------|-----------------------------|----------------|-----------------------------------|
| PB10GR121H       | GR          | Ocel            | 3/8"                         | 9.53 mm                     | #6 Concentric  | 4.67mm                            |
| PB10GR181H       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #6 Concentric  | 4.67mm                            |
| PB10GT161H       | GT          | Copper-bonded   | 5/8"                         | 14.3 mm                     | #6 Concentric  | 4.67mm                            |
| PB10GT181H       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #6 Concentric  | 4.67mm                            |
| PB10GR181V       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #2 Concentric  | 7.42mm                            |
| PB10GT181V       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #2 Concentric  | 7.42mm                            |
| PB13GY181V       | GY          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #2 Concentric  | 7.42mm                            |
| PB19GY181V       | GY          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #2 Concentric  | 7.42mm                            |
| PB10GR182C       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 1/0 Concentric | 9.47mm                            |
| PB10GS352C       | GS          | Ocel            | 7/8"                         | 22.23 mm                    | 1/0 Concentric | 9.47mm                            |
| PB10GT182C       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 1/0 Concentric | 9.47mm                            |
| PB10GR162G       | GR          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 2/0 Concentric | 10.62mm                           |
| PB10GR182G       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 2/0 Concentric | 10.62mm                           |
| PB10GT162G       | GT          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 2/0 Concentric | 10.62mm                           |
| PB10GT182G       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 2/0 Concentric | 10.62mm                           |
| PB19GY162G       | GY          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 2/0 Concentric | 10.62mm                           |
| PB19GY182G       | GY          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 2/0 Concentric | 10.62mm                           |
| PB10GR182Q       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 4/0 Concentric | 13.41mm                           |

| Katalogové číslo | Mold Family | Ground Rod Type | Ground Rod Diameter, Nominal | Ground Rod Diameter, Actual | Conductor Size       | Conductor Outer Diameter, Nominal |
|------------------|-------------|-----------------|------------------------------|-----------------------------|----------------------|-----------------------------------|
| PB10GT162Q       | GT          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 4/0 Concentric       | 13.41mm                           |
| PB10GT182Q       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 4/0 Concentric       | 13.41mm                           |
| PB10GT222Q       | GT          | Copper-bonded   | 1"                           | 23.22 mm                    | 4/0 Concentric       | 13.41mm                           |
| PB10GT332Q       | GT          | Ocel            | 3/4"                         | 19.05 mm                    | 4/0 Concentric       | 13.41mm                           |
| PB13GY162Q       | GY          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 4/0 Concentric       | 13.41mm                           |
| PB13GY182Q       | GY          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 4/0 Concentric       | 13.41mm                           |
| PB19GY162Q       | GY          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 4/0 Concentric       | 13.41mm                           |
| PB19GY182Q       | GY          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 4/0 Concentric       | 13.41mm                           |
| PB13GV169F       | GV          | Copper-bonded   | 5/8"                         | 14.3 mm                     | 19/#9 Copperweld     | 14.53mm                           |
| PB10GT182V       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 250 kcmil Concentric | 14.61mm                           |
| PB10GR184H       | GR          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #24                  | 15.37mm                           |
| PB10GT182S       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | 4/0 Ropelay          | 15.49mm                           |
| PB10GT184R       | GT          | Copper-bonded   | 3/4"                         | 17.32 mm                    | #24 Ropelay          | 22.4mm                            |
| PB10GF223S       | GF          | Copper-bonded   | 1"                           | 23.22 mm                    | 500 kcmil Ropelay    | 26.42mm                           |
| PB60GG3S22       | GG          | Copper-bonded   | 1"                           | 23.22 mm                    | 500 kcmil Ropelay    | 26.42mm                           |

## DALŠÍ PODROBNOSTI O PRODUKTU

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a PB10GR162G becomes XLPB10GR162G). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example,

PB90 becomes XLPB90).

A gap between conductors may be required. See mold tag for more information.

| XXXX-XX-XX-XX-L-M-W |                 |                                                                                         |
|---------------------|-----------------|-----------------------------------------------------------------------------------------|
| XXXX                | Price Key       |                                                                                         |
| XX                  | Mold Family     |                                                                                         |
| XX                  | Ground Rod Code |                                                                                         |
| XX                  | Conductor Code  |                                                                                         |
| L*                  | Split Crucible  | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M*                  | Mold Only       |                                                                                         |
| W*                  | Wear Plates     | Reduce mechanical abrasion of molds at cable entry points                               |

\* Empty if none

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Naše portfolio silných značek:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE