


# Cable to Rebar, Rail



nVent ERICO Cadweld applications for railway properties utilize the nVent ERICO Cadweld Plus F80 and the nVent ERICO Cadweld F80 welding material alloys. nVent ERICO Cadweld exothermically welded connections are engineered to provide a permanent, molecular bond that will not loosen or corrode, enabling connection of dissimilar materials. The connections are designed to perform for the life of the conductor and/or installation. The nVent ERICO Cadweld connection has a current carrying capacity equal to or greater than that of the conductor and will withstand repeated fault currents without failing during operation. Once completed, installers can clearly ensure quality by visually inspecting the new connection.

## DIAGRAMS



## VLASTNOSTI

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

## SPECIFIKACE

Table 1/1

| Katalogové číslo | Mold Family | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Conductor Size | Conductor Outer Diameter, Nominal |
|------------------|-------------|--------------------|----------------|--------------------|----------------|-----------------------------------|
| SB41RR531L       | RR          | 16 mm              | #5             | 15M                | #4 Concentric  | 5.89mm                            |

| Katalogové číslo | Mold Family | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Conductor Size | Conductor Outer Diameter, Nominal |
|------------------|-------------|--------------------|----------------|--------------------|----------------|-----------------------------------|
| PB10RR532Q       | RR          | 16 mm              | #5             | 15M                | 4/0 Concentric | 13.41mm                           |

## DALŠÍ PODROBNOSTI O PRODUKTU

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a PB10GR162G becomes XLPB10GR162G). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, PB90 becomes XLPB90).

Rebar material characteristics and location of weld must be considered when selecting connections to rebar.

| XXXX-XX-XX-XX-L-M-W |                |                                                                                         |
|---------------------|----------------|-----------------------------------------------------------------------------------------|
| XXXX                | Price Key      |                                                                                         |
| XX                  | Mold Family    |                                                                                         |
| XX                  | Rebar Code     |                                                                                         |
| XX                  | Conductor Code |                                                                                         |
| L*                  | Split Crucible | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M*                  | Mold Only      |                                                                                         |
| W*                  | Wear Plates    | Reduce mechanical abrasion of molds at cable entry points                               |

\* Empty if none

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**