

# Varistar LHX+ 45 In-Rack

## Data Solutions

Varistar LHX+ In-Rack coolers are designed to deliver localized energy efficient cooling to the equipment in installations where the ambient air is not filtered or temperature controlled. The device is IP54 and connects to attached Varistar CP cabinet into a sealed combo so no air is exchanged with the room.

The cooling system is integrated into a Varistar CP mobile frame for ideal side by side connection to Varistar CP racks. The cooler comes with solid front and rear doors. It incorporates a cold air plenum in the front and warm air plenum in the rear. The integrated fans move the warm exhaust air from the warm air plenum through an air to water heat exchanger where the heat is transferred to a water circuit. The air is then provided into the cold air plenum towards the equipment.

Varistar LHX+ 45 In-Rack Cooler

### VLASTNOSTI

In-row air/liquid cooler optimized for cooling of closed racks

Hot-swappable components simplify repair and maximize availability

Designed for efficient operation at increased facility water temperatures

Combination with direct to chip liquid cooling

Modular standard - easy to adapt to individual requirements

Minimum changes between In-Row and LHX+ (In-Rack) design - simplifies planning, layout and specification

Fans, power supplies, controller and control valve all are hot-swappable

Automatic fan speed and valve opening control

7" high resolution touch screen interface

Hydraulic and electric connection through top or bottom

Monitoring via Ethernet interface (Web browser, Modbus TCP, SNMP v2c) and Modbus RTU

### SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Produktová řada	Šířka	Hloubka	Výška	Supply Voltage
------------------	--------------	-----------------	-------	---------	-------	----------------

10630-100	Air/Liquid Heat Exchanger	Varistar	300mm	1000mm	2000mm	200 – 240V
10630-101	Air/Liquid Heat Exchanger	Varistar	300mm	1200mm	2000mm	200 – 240V

Table 2/2

Katalogové číslo	Coolant Feed	Povrchová úprava	Materiál	Množství v balení	Stupeň krytí	Rack Height
10630-100	Top, Bottom	Strukturovaný Práškový	Ocel	1	IP55	42U
10630-101	Top, Bottom	Strukturovaný Práškový	Ocel	1	IP55	42U

## DALŠÍ PODROBNOSTI O PRODUKTU

For trouble-free operation of the air/liquid heat exchanger the quality requirements of the coolant must be maintained; The selection of appropriate anti-corrosion and frost protection agents depends on the environment in which the unit is used and on the external chiller.

At coolant temperatures below 14 °C, there is an increased risk of condensation. We recommend using a condensate management package.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**