


Ground Rod to Lug or Busbar




nVent ERICO Cadweld graphite molds are designed and engineered for thousands of connection styles and conductor combinations.

CERTIFICATIONS



DIAGRAMS



VLASTNOSTI

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

Mold Families LA and LE can be used with straight or offset lugs

SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Mold Family	Ground Rod Type	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual	Lug/Busbar Size
LAC18EK		LA (To Ground Rod)	Copper-bonded	3/4"	17.3 mm	1/4" x 3" and wider
CSE14EG		CS	Ocel	1/2"	12.83 mm	1/4" x 1 1/2"
CMC14EAJ		CM	Ocel	1/2"	12.83 mm	4 mm x 25 mm
CMC14EAL		CM	Ocel	1/2"	12.83 mm	4 mm x 40 mm
CMC14EAM		CM	Ocel	1/2"	12.83 mm	4 mm x 50 mm
CMC14FAM		CM	Ocel	1/2"	12.83 mm	5 mm x 50 mm
CNC14EAJ		CN	Ocel	1/2"	12.83 mm	4 mm x 25 mm
CNC14EAM		CN	Ocel	1/2"	12.83 mm	4 mm x 50 mm
CSE16EAJ		CS	Copper-bonded	5/8"	14.3 mm	4 mm x 25 mm
CSE16EAM		CS	Copper-bonded	5/8"	14.3 mm	4 mm x 50 mm
CMC16CAJ		CM	Copper-bonded	5/8"	14.3 mm	3 mm x 25 mm
CMC16CAM		CM	Copper-bonded	5/8"	14.3 mm	3 mm x 50 mm
CMC16EAJ		CM	Copper-bonded	5/8"	14.3 mm	4 mm x 25 mm
CMC16EAL		CM	Copper-bonded	5/8"	14.3 mm	4 mm x 40 mm
CMC16EH		CM	Copper-bonded	5/8"	14.3 mm	1/4" x 2"
CMC16PAJ		CM	Copper-bonded	5/8"	14.3 mm	6 mm x 25 mm
CMC16PAL		CM	Copper-bonded	5/8"	14.3 mm	6 mm x 40 mm

Katalogové číslo	Article Number	Mold Family	Ground Rod Type	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual	Lug/Busbar Size
CMC16PAM		CM	Copper-bonded	5/8"	14.3 mm	6 mm x 50 mm
CNC16CAJ		CN	Copper-bonded	5/8"	14.3 mm	3 mm x 25 mm
CNC16CAK		CN	Copper-bonded	5/8"	14.3 mm	3 mm x 30 mm
CNC16EAM		CN	Copper-bonded	5/8"	14.3 mm	4 mm x 50 mm
CNC16FAL		CN	Copper-bonded	5/8"	14.3 mm	5 mm x 40 mm
CPC16BAH		CP	Copper-bonded	5/8"	14.3 mm	2 mm x 20 mm
CPC16CAJ		CP	Copper-bonded	5/8"	14.3 mm	3 mm x 25 mm and wider
CPC16EAJ		CP	Copper-bonded	5/8"	14.3 mm	4 mm x 25 mm and wider
CQR16CAH		CQ	Copper-bonded	5/8"	14.3 mm	3 mm x 20 mm
CRC16CE		CR	Copper-bonded	5/8"	14.3 mm	1/8" x 1"
CRC16EK		CR	Copper-bonded	5/8"	14.3 mm	1/4" x 3" and wider
CRC16FAM		CR	Copper-bonded	5/8"	14.3 mm	5 mm x 50 mm and wider
CRC16PAM		CR	Copper-bonded	5/8"	14.3 mm	6 mm x 50 mm and wider
CMCP160CAJ		CM	Ocel	16"	16 mm	3 mm x 25 mm
CRCP160CAJ		CR	Ocel	16"	16 mm	3 mm x 25 mm
CMC18CAJ		CM	Copper-bonded	3/4"	17.32 mm	3 mm x 25 mm
CMC18CAL		CM	Copper-bonded	3/4"	17.32 mm	3 mm x 40 mm
CNC18CAJ		CN	Copper-bonded	3/4"	17.32 mm	3 mm x 25 mm

Katalogové číslo	Article Number	Mold Family	Ground Rod Type	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual	Lug/Busbar Size
CNC18CAK		CN	Copper-bonded	3/4"	17.32 mm	3 mm x 30 mm
CNC18CAL		CN	Copper-bonded	3/4"	17.32 mm	3 mm x 40 mm
CNC18EAL		CN	Copper-bonded	3/4"	17.32 mm	4 mm x 40 mm
CPC18CAJ		CP	Copper-bonded	3/4"	17.32 mm	3 mm x 25 mm and wider
CPC18EAJ		CP	Copper-bonded	3/4"	17.32 mm	4 mm x 25 mm and wider
CRC18BAL		CR	Copper-bonded	3/4"	17.32 mm	2 mm x 40 mm and wider
CRC18EAL		CR	Copper-bonded	3/4"	17.32 mm	4 mm x 40 mm and wider
CRC18EH		CR	Copper-bonded	3/4"	17.32 mm	1/4" x 2" and wider
CRD18EK		CR	Copper-bonded	3/4"	17.32 mm	1/4" x 3" and wider
CNCP180FAM		CN	Ocel	18"	18 mm	5 mm x 50 mm
CQRP190CAJ		CQ	Ocel	19"	19 mm	3 mm x 25 mm
CMCP200CAJ	238133	CM	Ocel	20"	20 mm	3 mm x 25 mm
CNCP200CAK		CN	Ocel	20"	20 mm	3 mm x 30 mm
CQFP200FAN		CQ	Ocel	20"	20 mm	5 mm x 60 mm
CQRP200PAJ		CQ	Ocel	20"	20 mm	6 mm x 25 mm
CMC22CAJ		CM	Copper-bonded	1"	23.22 mm	3 mm x 25 mm
CMD22FAM		CM	Copper-bonded	1"	23.22 mm	5 mm x 50 mm

Table 2/2

Katalogové číslo	Article Number	Certifications
LAC18EK		
CSE14EG		
CMC14EAJ		
CMC14EAL		
CMC14EAM		
CMC14FAM		
CNC14EAJ		
CNC14EAM		
CSE16EAJ		
CSE16EAM		
CMC16CAJ		
CMC16CAM		
CMC16EAJ		
CMC16EAL		
CMC16EH		
CMC16PAJ		
CMC16PAL		
CMC16PAM		

Katalogové číslo	Article Number	Certifications
CNC16CAJ		
CNC16CAK		
CNC16EAM		
CNC16FAL		
CPC16BAH		
CPC16CAJ		
CPC16EAJ		
CQR16CAH		
CRC16CE		
CRC16EK		
CRC16FAM		
CRC16PAM		
CMCP160CAJ		
CRCP160CAJ		
CMC18CAJ		
CMC18CAL		
CNC18CAJ		
CNC18CAK		

Katalogové číslo	Article Number	Certifications
CNC18CAL		
CNC18EAL		
CPC18CAJ		
CPC18EAJ		
CRC18BAL		cUL, UL
CRC18EAL		
CRC18EH		
CRD18EK		
CNCP180FAM		
CQRP190CAJ		
CMCP200CAJ	238133	
CNCP200CAK		
CQFP200FAN		
CQRP200PAJ		
CMC22CAJ		
CMD22FAM		

DALŠÍ PODROBNOSTI O PRODUKTU

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150

becomes XL150).

A gap between conductors may be required. See mold tag for more information.

XX-X-XX-XX-L-M-W		
XX	Mold Family	
X	Price Key	
XX	Ground Rod Code	
XX	Lug/Busbar Size	
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning
M*	Mold Only	
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points

* Empty if none

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE