

MTCA.4 System for 12 Double Full-Size AMC Modules



The system is designed for high-performance, high availability applications. The hot-swap fan modules with EMMC in pull configuration ensure that the front and rear slots are properly cooled. The fan speed is adjustable via the MCH. The separate JSM installation space prevents an AMC slot from being occupied by a JTAG module. The system can take up to four power modules to ensure a sufficient power supply for demanding applications. The backplane features clock and trigger lines.

CERTIFICATIONS



VLASTNOSTI

In accordance with MTCA.4 R1.0 specification

84 HP system for 12 double Full-Size AdvancedMC modules, 2 Single Full-Size MCHs, and 4 / 2 Single Full-Size power modules

6 rear transition module slots for Double Full-Size RTMs

1 Single Full-Size slot for a JTAG switch module (JSM)

Backplane with dual-star topology

Optional fan speeds for front and rear sections can be separately adjusted via the MCH

2 hot-swap fan modules with cooling unit manager (CU EMMC)

Air filter accessible from the front

SPECIFIKACE

Table 1/3

Katalogové číslo	Product Type	Number of Slots	Typ	Backplane Type	Data Transfer	Power per Slot
------------------	--------------	-----------------	-----	----------------	---------------	----------------

11890-170	System	12	19" Rack Mount	MTCA.4 Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-156	System	12	19" Rack Mount	CMS Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-152	System	12	19" Rack Mount	MTCA.4 Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-119	System	12	19" Rack Mount	CMS Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W

Table 2/3

Katalogové číslo	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O	Complies With
11890-170	Front to Rear	9U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0
11890-156	Front to Rear	9U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0
11890-152	Bottom to Top	7U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0
11890-119	Bottom to Top	7U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0

Table 3/3

Katalogové číslo	Hloubka	Množství v balení	Rychlé odeslání
11890-170	373mm	1	Ne
11890-156	373mm	1	Ne
11890-152	373mm	1	Ne
11890-119	373mm	1	Ne

[DALŠÍ PODROBNOSTI O PRODUKTU](#)

2 Power Supplies are required to operate the system.

Modified systems available on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE