

ABS Adjustable Busbar Support Insulator Module

Power Utilities



CERTIFICATIONS



VLASTNOSTI

Modules provide flexibility to select distance between phases and supports

Extremely robust construction

Halogen free insulators

RoHS compliant

SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Max Working Voltage, IEC (Ui)	Working Temperature	Typical Application Current Rating	Busbars per Phase	Busbar Thickness
ABS1-5MOD	560860	1,000 VAC, 1,500 VDC	-40 to 130 °C	1,700 A Max	1	5 mm


Table 2/2

Katalogové číslo	Article Number	Busbar Width	Width (W)	Unit Weight
ABS1-5MOD	560860	50 – 125 mm	74 mm	0.640 kg

DALŠÍ PODROBNOSTI O PRODUKTU

ABS Adjustable Busbar Support High Ampacity Kit available to support up to 200 mm (7.87") busbar width for applications up to 7400 A.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE