

# **Guardian Management Gateway**

# **Data Solutions**



The nVent SCHROFF Guardian Management Gateway is an environmental monitoring platform designed to sense, track, store and alarm health and security parameters in an IT data center infrastructure.

The heart of the platform is a compact control unit of 1 U in height/depth and 250 mm in width, it can be installed as 19" unit or into any available space in a data center rack.

The Management Gateway offers three sensor management ports with each port being able to monitor up to 16 sensor devices with a total cable length of 40 meters per port, allowing a single Management Gateway unit to monitor multiple racks or complete rack aisles.

Besides monitoring physical parameters like temperature, humidity, smoke, door status or water intrusion, the Management Gateway can also monitor nVent SCHROFF RackChiller and In- Row Coolers – with an easy plug and play installation.

Set-up of the Management Gateway with security features, sensor configuration, user management, alarm and log management can easily done through a built in Web Interface.

Main access to the Management Gateway is through the 1 GBE Network interface, supporting industry standard protocols like SNMP, SMTP, HTTPS, BACnet, Modbus/TCP and HPI

#### **CERTIFICERINGER**





#### **FUNKTIONER**

Data Center environmental monitoring platform

Compact design, fits anywhere in a data center rack

Web browser GUI for setup, monitoring and maintenance

Three management ports to connect external sensors and Modbus devices

Up to 16 sensors or devices per management port with a total cable length of up to 40 m  $\,$ 

Auto orientation LCD touch display

Supports industry standard network protocols (HTTPS, SNMP, SMTP, BACnet, Modbus/TCP and HPI)

## **SPECIFIKATIONER**

Table 1/2										
Katalognumme r	Туре	Rack Height	Højde	Bredde	Dybde	Indgangsspæn ding AC				
11079-000	Base Unit Management Gateway	1U	45mm	250mm	45mm					
11079-001	Base Unit Management Gateway	1U	45mm	350mm	45mm	100 – 240V				

Table 2/2									
Katalognumme r	Indgangsspæn ding DC	Omgivelsestem peratur	Materiale	Finish	Relative Humidity	Certificeringer			
11079-000	12V min	5 - 60°C	Aluminium	Struktur Pulvermaling	5% to 90%, Noncondensing	RoHS, WEEE			
11079-001		5 - 60°C	Aluminium	Struktur Pulvermaling	5% to 90%, Noncondensing				

## **ADVARSEL**

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY **HOFFMAN TRACHTE ERICO SCHROFF ILSCO**