

RackChiller Rear Door Control Unit, Passive

Data Solutions



The Control Unit enriches the passive RackChiller Rear Door. It connects to the 4 built-in air temperature sensors and the motorized coolant valve 23130-607. This enables the cooler to control the coolant air flow based on a chilled (supply) air temperature setpoint. It provides advanced remote monitoring functionality and various setup features.

CERTIFICERINGER



FUNKTIONER

Coolant flow control based on chilled (supply) air temperature setpoint. More control features with water control package 21130-608

Precise flow control against setpoint with parametric PID loop

Remote monitoring through built-in Web Server or BMS protocols (Modbus TCP, SNMP v2c)

Optional external display and keypad 21130-599

Languages: English, German, French

Power Supply: 90 - 260 VAC

SPECIFIKATIONER

Table 1/1

Katalognummer	Farve
23130-594	Black Grey

YDERLIGERE PRODUKTOPLYSNINGER

For trouble-free operation it is recommended to use the water connection set and the optional accessories.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE