

Copper-Bonded Ground Rod, Threaded



CERTIFICERINGER



FUNKTIONER

Cold-rolled threads with continuous, unbroken grain flows preserve copper coating and are stronger than cut threads

99.9% pure electrolytic copper coating

Rods have a high carbon steel core and tip that provide superior strength when driving

Copper coating will not crack when bent or tear when driven

Minimum copper coating of 10 mils on rods listed to UL® 467

nVent ERICO name, length, diameter and part number is roll-stamped within 12" (304,8 mm) of chamfered end

UL logo and control number where applicable stamped on each rod for easy inspection after installation

SPECIFIKATIONER

Materiale:	Copper-Bonded Steel
Thread Location:	Pointed and Chamfered Ends
Tensile Strength:	552 MPa Min

Table 1/2

Katalognummer	Artikelnummer	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)	Length (L)	Plating Thickness
---------------	---------------	------------------------------	---------------------------------	------------------	------------	-------------------

631300		1/2"	12.8 mm	9/16" UNC	3m	254µm
631303		1/2"	12.8 mm	9/16" UNC	3m	330µm
631340		1/2"	12.8 mm	9/16" UNC	1.2m	254µm
631350		1/2"	12.8 mm	9/16" UNC	1.5m	254µm
631360		1/2"	12.8 mm	9/16" UNC	1.8m	254µm
631380		1/2"	12.8 mm	9/16" UNC	2.4m	254µm
635800		5/8"	14.2 mm	5/8" UNC	3m	254µm
635803		5/8"	14.2 mm	5/8" UNC	3m	330µm
635830		5/8"	14.2 mm	5/8" UNC	0.9m	254µm
635840		5/8"	14.2 mm	5/8" UNC	1.2m	254µm
635843		5/8"	14.2 mm	5/8" UNC	1.2m	330µm
635850		5/8"	14.2 mm	5/8" UNC	1.5m	254µm
635860		5/8"	14.2 mm	5/8" UNC	1.8m	254µm
6358660		5/8"	14.2 mm	5/8" UNC	2m	254µm
635870		5/8"	14.2 mm	5/8" UNC	2.1m	254µm
635880	635880	5/8"	14.2 mm	5/8" UNC	2.4m	254µm
635883		5/8"	14.2 mm	5/8" UNC	2.4m	330µm
633400		3/4"	17.3 mm	3/4" UNC	3m	254µm
633403		3/4"	17.3 mm	3/4" UNC	3m	330µm

633415		3/4"	17.3 mm	3/4" UNC	4.6m	254µm
633430		3/4"	17.3 mm	3/4" UNC	0.9m	254µm
6334330		3/4"	17.3 mm	3/4" UNC	1m	254µm
633440		3/4"	17.3 mm	3/4" UNC	1.2m	254µm
633450		3/4"	17.3 mm	3/4" UNC	1.5m	254µm
633460		3/4"	17.3 mm	3/4" UNC	1.8m	254µm
633463		3/4"	17.3 mm	3/4" UNC	1.8m	330µm
633470		3/4"	17.3 mm	3/4" UNC	2.1m	254µm
633480	633480	3/4"	17.3 mm	3/4" UNC	2.4m	254µm
634400		1"	23.2 mm	1" UNC	3m	254µm

Table 2/2				
Katalognummer	Artikelnummer	Unit Weight	Complies With	Certificeringer
631300		3.1 kg	ANSI®/NEMA® GR1	CSA-US, UL, CSA, cUL
631303		3.2 kg	ANSI®/NEMA® GR1	cUL, UL
631340		1.2 kg		
631350		1.6 kg		
631360		1.9 kg		
631380		2.4 kg	ANSI®/NEMA® GR1	UL
635800		3.8 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	CSA, UL, CSA-US, RUS, cUL
635803		3.9 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	RUS, UL, cUL

Katalognummer	Artikelnummer	Unit Weight	Complies With	Certificeringer
635830		1.2 kg	IEC® EN 62561-2	
635840		1.5 kg	IEC® EN 62561-2	
635843		1.5 kg	IEC® EN 62561-2	
635850		1.9 kg	IEC® EN 62561-2	
635860		2.3 kg	IEC® EN 62561-2	
6358660		2.48 kg	IEC® EN 62561-2	
635870		2.9 kg	IEC® EN 62561-2	
635880	635880	3 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	RUS, UL
635883		3 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	RUS, UL
633400		5.7 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	UL, cUL, CSA-US, RUS, CSA
633403		5.7 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	cUL, UL
633415		8.5 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	UL, cUL
633430		1.7 kg	IEC® EN 62561-2	
6334330		2.79 kg	IEC® EN 62561-2	
633440		2.2 kg	IEC® EN 62561-2	
633450		2.8 kg	IEC® EN 62561-2	
633460		3.2 kg	IEC® EN 62561-2	
633463		3.2 kg	IEC® EN 62561-2	


Katalognummer	Artikelnummer	Unit Weight	Complies With	Certificeringer
633470		3.9 kg	IEC® EN 62561-2	
633480	633480	4.4 kg	ANSI®/NEMA® GR1, IEC® EN 62561-2	UL, RUS
634400		10 kg	ANSI®/NEMA® GR1	CSA-US, UL, cUL, CSA

YDERLIGERE PRODUKTOPLYSNINGER

For rods to be listed to UL® 467, they must be at least 8' (2.44 m) in length.

IEC® EN 62561-2 supercedes EN 50164-2.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including nickel, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE