

DT1 DIN Rail Surge Protection Class I+II 12.5 kA, 4+0 Mode



CERTIFICERINGER



FUNKTIONER

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


SPECIFIKATIONER

Katalognummer	DT130040R	DT148040R
Nominal System Voltage (Un)	240 V	400 V
Max Continuous Operating Voltage (Uc)	300 V	480 V
Nominal Discharge Current (In), IEC	20kA 8/20 μ s	20kA 8/20 μ s
Max Discharge Current (Imax), IEC	50kA 8/20 μ s	50kA 8/20 μ s
Impulse Current (Iimp)	12.5kA 10/350 μ s	10kA 10/350 μ s
Voltage Protection Level (Up)	1400V	2000V

Katalognummer	DT130040R	DT148040R
Response Time	25 ns Max	25 ns Max
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz	50 - 60 Hz
Short Circuit Current Rating (Isccr)	25kA 50kA	25kA 50kA
Protection Modes	L-N N-PE	L-N N-PE
Temporary Over Voltage 120 min (Ut/mode)	442 V Safe Fail	762 V Safe Fail
Temporary Over Voltage Withstand 5 s (Ut)	337V	581V
Voltage Protection Rating (VPR)	900V	1500V
Nominal Discharge Current (In), UL	20kA 8/20 µs	20kA 8/20 µs
Replacement Module	DT1300M	DT1480M
Short Circuit Current Rating (SCCR)	150kA	200kA
Technology	Thermal Disconnect	Thermal Disconnect
Connection, Solid	35 mm ² Max	35 mm ² Max
Connection, Stranded	25 mm ² Max	25 mm ² Max
Torque (TQ)	4.5 N·m	4.5 N·m
Humidity	5 - 95	5 - 95
Temperature	-35 to 85 °C	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC 1 A @ 125 VAC 1 A @ 250 VAC	0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC 1 A @ 125 VAC 1 A @ 250 VAC
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Dybde (D)	92mm	92mm
Height (H)	90 mm	90 mm
Width (W)	72 mm	72 mm
Unit Weight	0.69 kg	0.77 kg
Certification Details	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA

Katalognummer	DT130040R	DT148040R
Complies With	EN 61643-11 Type 1, Type 2 IEC® 61643-11 Class I, Class II	EN 61643-11 Type 1, Type 2 IEC® 61643-11 Class I, Class II

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE